







REV
A

DTM06-12S*-EE04

REVISIONS

SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. PI9500	8/22/07	RDR
A	REVISED PER E.O. PI9776	4-7-08	RDR

HIGH TEMPERATURE IDENTIFIER



SEE SHEET 2 FOR OTHER KEY ARRANGEMENTS.

7. PART MODIFICATION: PLUG IS RATED AT 150°C (COLOR: BLACK).

6. MATERIAL - HOUSING: PLASTIC; GROMMET: RUBBER.

5. CONNECTOR DESIGNED TO BE USED WITH DTM04-12P*-**** RECEPTACLES.
(*) = A,B,C,D KEYS, (****) = ALL HIGH TEMPERATURE MODIFICATIONS.
CONSULT FACTORY FOR MODIFICATIONS.




FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION
CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.

3. SECONDARY WEDGE LOCK SOLD SEPARATELY: WM-12S.

2. DIMENSION TOLERANCE: $\pm .025$ [.64].

1. DIMENSIONS ARE IN INCHES [mm].

NOTES: UNLESS OTHERWISE SPECIFIED



CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIRE RANGE [mm ²] REF ONLY
20	.053 [1.35]	.120 [3.05]	16-22 AWG [1.0-0.5]

SIGNATURE & DATE	
DR	D. MEYER 05/02/07
CHK	205/04/04/4/07/08
PE	Paula Gamm 4/7/08
APPD	D. Meyer 4/14/08
SCALE	NONE

PLUG
12 CONTACTS, SIZE 20
A,B,C,D KEYS
-EE04 MOD
DTM SERIES

ENVELOPE

EP 172

MATL
CODE

3850 INDUSTRIAL AVE.
HEMET, CA 92545

DEUTSCH
INDUSTRIAL

B









DTM06-12S*-EE04

DWG
SIZE

CODE
11139

SHEET 1 OF 2

REV A	DTM06-12S*EE04	REVISIONS			
		SYM	DESCRIPTION	DATE	APPROVED
		A	SEE SHEET 1	5/12/08	Dm



DTM06-12SA-EE04
KEY -A-
COLOR: BLACK

DTM06-12SB-EE04
KEY -B-
COLOR: BLACK

DTM06-12SC-EE04
KEY -C-
COLOR: BLACK

DTM06-12SD-EE04
KEY -D-
COLOR: BLACK

NOTES:

SIGNATURE & DATE		PLUG 12 CONTACTS, SIZE 20 A,B,C,D KEYS -EE04 MOD DTM SERIES ENVELOPE	EP 172	NATL. CODE
DR	D. MEYER 05/02/07		 3850 INDUSTRIAL AVE. HEMET, CA 92545	DTM06-12S*-EE04
CHK	<i>[Signature]</i> 5/12/08			
PE	<i>[Signature]</i> 5/12/08			
APPD	<i>[Signature]</i> 5/12/08		DWG SIZE	
SCALE	NONE		CODE 11139	SHEET 2 OF 2