



SAFETY ORGANIZATIONS	
THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:	
	UL RECONGNIZED: UL 1283
	CSA CERTIFIED: CSA C22.2 No. 8
	VDE APPROVED: EN 60939-2
OPERATING SPECIFICATIONS	
LINE CURRENT/VOLTAGE:	20 AMP, 120/250 VAC
CSA & VDE:	20 AMP/40°C, 250 VAC
OPERATING AMBIENT TEMP. RANGE: -10°C TO +40°C @ RATED CURRENT, I _r . IN AN AMBIENT, T _a , HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, I _o , IS AS FOLLOWS:	
$I_o = I_r \sqrt{\frac{100 - T_a}{60}}$	
LINE CURRENT/VOLTAGE:	20 AMP, 120/250 VAC
UL:	20 AMP/25°C, 120/250 VAC
OPERATING AMBIENT TEMP. RANGE: -10°C TO +25°C @ RATED CURRENT, I _r . IN AN AMBIENT, T _a , HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, I _o , IS AS FOLLOWS:	
$I_o = I_r \sqrt{\frac{100 - T_a}{75}}$	
LINE FREQUENCY: 50-60Hz	
MAXIMUM LEAKAGE CURRENT, EACH LINE TO GROUND:	
0.22mA @ 120V, 60Hz	
0.38mA @ 250V, 50Hz	
RELIABILITY SPECIFICATIONS:	
STORAGE TEMPERATURE: -40°C TO +85°C	
HUMIDITY: 21 DAYS @ 40°C 95% RH.	
CURRENT OVERLOAD TEST: 6 TIMES I _r FOR 8 SECONDS	
RECOMMENDED RECEIVING INSPECTION HIPOT:	
LINE TO GROUND: 1500 VAC FOR 1 MINUTE	
LINE TO LINE: 1450 VDC FOR 1 MINUTE	
FILTER APPROVAL:	
THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.	
TEST SPECIFICATIONS:	
INDUCTANCE: 6.0 mH NOMINAL	
CAPACITANCE: (MEASURED @ 1kHz, 0.250VAC MAX., 25°C±1°C)	
LINE TO GROUND: .0056 µF ±20%	
LINE TO LINE: 4.4 µF ±20%	
DISCHARGE RESISTOR: 73.3 KΩ	
L/G AND L/L I.R.	
NO DISCHARGE RESISTOR: 6000MΩ (MIN.) @ 100VDC, 20°C AND 50% RH	



50 Ω - 50 Ω (MINIMUM) INSERTION LOSS												PARTS SHALL COMPLY WITH TYCO ELECTRONICS 138-702 SPECIFICATION FOR HAZARDOUS SUBSTANCES			
FREQUENCY Hz	.01	.02	.05	.15	.5	1	5	10	30	-	-	UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE ±0.63 MATERIAL & FINISH: AS SUPPLIED			
COMMON dB	6	10	8	39	60	65	65	65	55	-	-	NOTES:			
DIFF. dB	15	20	20	46	65	70	65	60	60	-	-				
THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA USA.												TE Connectivity			
CUSTOMER DRAWING												TE PART NO: 6609048-9			
SHEET SIZE: B THIRD ANGLE PROJECTION												DIMENSIONS IN MILLIMETERS			
SCALE: 5/8												DATE: 01OCT93			
DRW. BY: LJO												DRG: TAM			
20EQ1 P.ekd Rev Layer 2												DRAWING NUMBER: 20EQ1			
												REV. P			