


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	R1	ECR-25-234165	12FEB2025	ABS	DR



- 1 TIN PL .000150 MIN THK PER ASTM B 545
- 2 PART NO: 324461; .071 LB.
PART NO: 1-324461-0; .071 LB.
PART NO: 2-324461-2; .082 LB.
PART NO: 2-324461-3; .082 LB.
- 3 CLEANED, UNPLATED
- 4 PRELIMINARY - NOT FOR PRODUCTION
- 5 .045 MAX BURR ALLOWED INSIDE THE WIRE BARREL ID IN AREA OF SIGHT HOLE.

OBSOLETE	.72	.97	1.89	190,000-231,000	1	COPPER ASTM-B-75 ANNEALED	2-324461-3
					3		2-324461-2
					3		1-324461-0
					1		324461
	.72	.72	1.65	CM			
	"C"	"B"	"A"	WIRE RANGE	FINISH	MATERIAL	PART No

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 4/24/89	TE Connectivity				
		CHK MS FEHER 4/24/89					
DIMENSIONS: INCHES		APVD WJ VOCKROTH 11/8/89	NAME SPLICE, BUTT, AMPPOWER WIRE SIZE: 4/0 AWG				
		PRODUCT SPEC					
		APPLICATION SPEC					
MATERIAL SEE TABLE		WEIGHT 2	SIZE A3	CAGE CODE 00779	DRAWING NO C-324461	RESTRICTED TO -	
FINISH SEE TABLE		CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	REV R1	