
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2012
© COPYRIGHT 2012 TE Connectivity ALL RIGHTS RESERVED.


LOC	DIST
FM	–


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	H3	ECR-15-002210	05MAR2015	GB	SzG
	H4	ECR-16-009474	21JUL2016	LSz	GB
	H5	ECR-20-010381	10DEC2021	KMD	MN
	H6	REVISED PER ECR-23-194789	11AUG2025	RK	DJ

-4 wie gezeichnet
AS SHOWN







H2 H3

Bemerkungen / Notes:

1. Teile in Lupolenbeutel luftdicht verpackt (500/1000 Sctk.)
   Parts must be airtight packaged in bags of lupolen (500/1000 pieces)

2 Geschmiert mit Gleitmittel Hellerine (Fa. Hellermanntyton)
direkt vor dem Einsetzen des Kontaktes
Lubricated with Hellerine 625 (Hellermanntyton) right before contact insertion

3 Kammer für Buschsenkontakt CIC. C1-2 od. Type III
Cavity for socket contact CIC. C1-2 or Type III


4 Dichtungstülle für Litzenleitung mit
Isolationsdurchmesser von 2.3-3.0mm
Seal for wire with isolationdiameter 2.3 - 3.0 mm 10

Dichtungstülle für Litzenleitung mit
Isolationsdurchmesser von 1.3-2.3 mm
Seal for wire with isolationdiameter 1.3 - 2.3 mm 11


5 Keying Form with the Mating Connector: Click Stop


6 Keying Form with the Mating Connector: Locking


3:1



1-..-2 wie gezeichnet
AS SHOWN







OBSOLETE	2-826886-2	H	SEAL 10	NEOPRENE	GREY	3	2.1
			O-RING	NEOPRENE	BLACK	1	3
			3 POS. SOCKET HOUSING	PA 6.6 GFV13	GREEN	1	4
H5 OBSOLETE	2-826886-1	H	SEAL 11	NEOPRENE	BLACK	3	2.2
			O-RING	NEOPRENE	BLACK	1	3
			3 POS. SOCKET HOUSING	PA 6.6 GFV13	NATURAL	1	4
OBSOLETE	1-826886-9	H	SEAL 10	NEOPRENE	GREY	3	2.1
			O-RING	NEOPRENE	BLACK	1	3
			3 POS. SOCKET HOUSING	PA 6.6 GFV13	NATURAL	1	4
	1-826886-8	H	SEAL 11	NEOPRENE	BLACK	3	2.2
			O-RING	NEOPRENE	BLACK	1	3
			3 POS. SOCKET HOUSING	PA 6.6 GFV13	BLACK	1	4
OBSOLETE	1-826886-7	H	SEAL 11	NEOPRENE	BLACK	3	2.2
			O-RING	NEOPRENE	BLACK	1	3
			3 POS. SOCKET HOUSING	PA 6.6 GFV13	YELLOW	1	4
OBSOLETE	1-826886-4	H	SEAL 10	NEOPRENE	GREY	3	2.1
			O-RING	NEOPRENE	BLACK	1	3
			3 POS. SOCKET HOUSING	PA 6.6 GFV13	YELLOW	1	4
OBSOLETE	1-826886-3	H	SEAL 10	NEOPRENE	GREY	3	2.1
			O-RING	NEOPRENE	BLACK	1	3
			3 POS. SOCKET HOUSING	PA 6.6 GFV13	RED	1	4
	1-826886-2	H	SEAL 10	NEOPRENE	GREY	3	2.1
			O-RING	NEOPRENE	BLACK	1	3
			3 POS. SOCKET HOUSING	PA 6.6 GFV13	BLACK	1	4
OBSOLETE	1-826886-1	H	–	–	–	–	–
			O-RING	NEOPRENE	BLACK	1	3
			3 POS. SOCKET HOUSING	PA 6.6 GFV13	BLACK	1	4
	826886-7	H	SEAL 11	NEOPRENE	BLACK	3	2.2
			O-RING	NEOPRENE	BLACK	1	3
			3 POS. SOCKET HOUSING	PA 6.6 GFV13	BLACK	1	1
OBSOLETE	826886-6	H	SEAL 10	NEOPRENE	GREY	3	2.1
			O-RING	NEOPRENE	BLACK	1	3
			3 POS. SOCKET HOUSING	PA 6.6 GFV13	YELLOW	1	1
OBSOLETE	826886-5	H	SEAL 10	NEOPRENE	GREY	3	2.1
			O-RING	NEOPRENE	BLACK	1	3
			3 POS. SOCKET HOUSING	PA 6.6 GFV13	RED	1	1
	826886-4	H	SEAL 10	NEOPRENE	GREY	3	2.1
			O-RING	NEOPRENE	BLACK	1	3
			3 POS. SOCKET HOUSING	PA 6.6 GFV13	BLACK	1	1
OBSOLETE	826886-1	H	–	–	–	–	–
			O-RING	NEOPRENE	BLACK	1	3
			3 POS. SOCKET HOUSING	PA 6.6 GFV13	BLACK	1	1
	ASSY NO	REV.	DESCRIPTION	MATERIAL	COLOUR	QTY.	ITEM NO

ACHTUNG !
Eine einwandfreie Funktion dieser Stecker kann nur bei Verwendung von Original-TEC -Teilen und genaur Einhaltung der Verarbeitungsvor - schriften garantiert werden.
CAUTION !

A faultless operation of this connectors can be guaranteed only if original TEC parts are used and exact observance of processing specifications.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm
0 PLC ±–
1 PLC ±–
2 PLC ±–
3 PLC ±–
4 PLC ±–
ANGLES ±1.5°

MATERIAL SEE LIST –
FINISH – –

DWN ADAMSKI 21OCT1982
CHK WENDLING 25OCT1982
APVD – –
PRODUCT SPEC – –
APPLICATION SPEC – –
WEIGHT –

TE Connectivity

NAME 3POS. ECONOSEAL SOCKET-HOUSING ASS'Y –

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-826886	

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV H6