





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
H7		REVISED PER ECN-22-163403	08JUL2022	WLS	VS
H8		REVISED PER ECN-23-240910	24NOV2023	WLS	VS
H9		REVISED PER ECN-24-279340	19AUG2024	WLS	JP
J		REVISED PER ECN-25-323497	02JUN2025	WLS	JP




- 1 MATERIAL;  
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.  
CONTACTS - BRASS.  
HOLDDOWNS - PHOSPHOR BRONZE.
- 2 DIMENSION APPLIES TO SOLDER TAIL SURFACES, HOLDDOWNS SURFACES AND STANDOFF SURFACES.
- 3 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 4 ALL SOLDER TAILS AND HOLDDOWNS.
- 5 PLATING;  
CONTACTS - 0.76µm MINIMUM GOLD,  
OR  
0.0762µm MINIMUM GOLD FLASH OVER 0.69µm MINIMUM PALLADIUM NICKEL,  
ON MATING AREA PER TE CONNECTIVITY'S DISCRETION,  
2.54µm MINIMUM MATTE TIN ON SOLDER TAIL.  
ALL OVER 1.27µm MINIMUM NICKEL.  
HOLDDOWNS - 2.54µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL.
- 6 SPECIAL PACKAGING : 1 PLASTIC BAG PER REEL, ALL REELS INTO THE BOX. OBSOLETE
- 7 REVERSED TAPE, SEE SPECIFICATION 114-13000. OBSOLETE
- 8 COUNTERPART RECOMMENDED IS PN 794617 (DASH ACCORDING TO NUMBER OF POSITION). OBSOLETE
- 9 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000. OBSOLETE

18.86	22.27	15.00	22.00	12	7-794629-2/6
12.86	16.27	9.00	16.00	8	6-794629-8/7
6.86	10.27	3.00	10.00	4	6-794629-4/7
36.86	40.27	33.00	40.00	24	5-794629-4
33.86	37.27	30.00	37.00	22	5-794629-2
30.86	34.27	27.00	34.00	20	5-794629-0
27.86	31.27	24.00	31.00	18	4-794629-8
24.86	28.27	21.00	28.00	16	4-794629-6
21.86	25.27	18.00	25.00	14	4-794629-4
18.86	22.27	15.00	22.00	12	4-794629-2
15.86	19.27	12.00	19.00	10	4-794629-0
12.86	16.27	9.00	16.00	8	3-794629-8
9.86	13.27	6.00	13.00	6	3-794629-6
6.86	10.27	3.00	10.00	4	3-794629-4
3.86	7.27	-	7.00	2	3-794629-2
DIM Y	DIM W	DIM Z	DIM X	NO. OF POSN.	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 19MAR2003	TE Connectivity																
DIMENSIONS: mm		CHK C. JONES 19MAR2003																	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. JONES 19MAR2003	NAME SMT, RIGHT ANGLE, SMT HOLDDOWN HDR, ASSY, 0.76Au or 0.69PdNi DUAL ROW, MICRO MATE-N-LOK TM																
<table border="1"> <tr><td>0 PLC</td><td>±</td></tr> <tr><td>1 PLC</td><td>±</td></tr> <tr><td>2 PLC</td><td>±0.20</td></tr> <tr><td>3 PLC</td><td>±</td></tr> <tr><td>4 PLC</td><td>±</td></tr> <tr><td>ANGLES</td><td>±1°</td></tr> <tr><td>FINISH</td><td></td></tr> </table>		0 PLC	±	1 PLC	±	2 PLC	±0.20	3 PLC	±	4 PLC	±	ANGLES	±1°	FINISH		PRODUCT SPEC 108-1836	SIZE 114-13000	CAGE CODE A200779	DRAWING NO C-794629
0 PLC	±																		
1 PLC	±																		
2 PLC	±0.20																		
3 PLC	±																		
4 PLC	±																		
ANGLES	±1°																		
FINISH																			
MATERIAL	1	5	WEIGHT -	SCALE 4:1	SHEET 1 OF 2														
CUSTOMER DRAWING			RESTRICTED TO -	REV J															

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-



KEYING BY POSITION SIZE



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 19MAR2003	TE Connectivity	
DIMENSIONS: mm		CHK C. JONES 19MAR2003		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. JONES 19MAR2003	NAME SMT, RIGHT ANGLE, SMT HOLDDOWN HDR, ASSY, 0.76Au or 0.69PdNi DUAL ROW, MICRO MATE-N-LOK	
		PRODUCT SPEC 108-1836	SIZE A2	CAGE CODE 0779
MATERIAL		APPLICATION SPEC 114-13000	DRAWING NO G-794629	RESTRICTED TO -
		WEIGHT -	SCALE 4:1	SHEET 2 OF 2
		CUSTOMER DRAWING	REV J	