


Captive Screws - 1/4-28 Thread					
✓	FCXXXX	Length (L)	H.D. +.015 -.000	S.L. +.010 -.010	D. +.010 -.000
	FC0253	5/8	9/16	1/4	3/32
	FC0254	11/16	9/16	5/16	3/32
	FC0255	3/4	9/16	3/8	3/32
	FC0256	13/16	9/16	7/16	3/32
	FC0257	7/8	9/16	1/2	3/32
	FC0258	15/16	9/16	9/16	3/32
	FC0259	1	9/16	5/8	3/32
	FC0260	1-1/16	9/16	11/16	3/32
	FC0261	1-1/8	9/16	3/4	3/32
	FC0262	1-3/16	9/16	13/16	3/32
	FC0263	1-1/4	9/16	7/8	3/32
	FC0264	1-5/16	9/16	15/16	3/32
	FC0265	1-3/8	9/16	1	3/32
	FC0266	1-7/16	9/16	1-1/16	3/32
	FC0267	1-1/2	9/16	1-1/8	3/32
	FC0268	1-9/16	9/16	1-3/16	3/32
	FC0269	1-5/8	9/16	1-1/4	3/32
	FC0270	1-11/16	9/16	1-5/16	3/32
	FC0271	1-3/4	9/16	1-3/8	3/32
	FC0272	1-13/16	9/16	1-7/16	3/32
	FC0273	1-7/8	9/16	1-1/2	3/32
	FC0274	1-15/16	9/16	1-9/16	3/32
	FC0275	2	9/16	1-5/8	3/32
	FC0276	5/8	3/4	1/4	1/8
	FC0277	11/16	3/4	5/16	1/8
	FC0278	3/4	3/4	3/8	1/8
	FC0279	13/16	3/4	7/16	1/8
	FC0280	7/8	3/4	1/2	1/8
	FC0281	15/16	3/4	9/16	1/8
	FC0282	1	3/4	5/8	1/8
	FC0283	1-1/16	3/4	11/16	1/8
	FC0284	1-1/8	3/4	3/4	1/8
	FC0285	1-3/16	3/4	13/16	1/8
	FC0286	1-1/4	3/4	7/8	1/8
	FC0287	1-5/16	3/4	15/16	1/8
	FC0288	1-3/8	3/4	1	1/8
	FC0289	1-7/16	3/4	1-1/16	1/8
	FC0290	1-1/2	3/4	1-1/8	1/8
	FC0291	1-9/16	3/4	1-3/16	1/8
	FC0292	1-5/8	3/4	1-1/4	1/8
	FC0293	1-11/16	3/4	1-5/16	1/8
	FC0294	1-3/4	3/4	1-3/8	1/8
	FC0295	1-13/16	3/4	1-7/16	1/8
	FC0296	1-7/8	3/4	1-1/2	1/8
	FC0297	1-15/16	3/4	1-9/16	1/8
	FC0298	2	3/4	1-5/8	1/8

Captive Screw Type 1 1/4-28 Thread



Create a part number:

Length	Material	Finish
FCXXXX	XX	XX
_____ - _____ - _____		

Source Control Drawing:
To be produced by
Fascomp Electronic Hardware

Material

✓	Material Code (XX)	
	B	Brass
	S	Steel
	SS	Stainless Steel

Compatible Finish (XX)

✓	B, S, SS	0 - Plain
	B, S	5 - Nickel Plate (QQ-N-290)
	B, S	12 - Zinc Clear (ASTM-B-633)
	B, S	16 - Electro Tin (MIL-T-10727 TYPE 1)
	SS	20 - Passivation (MIL-F-14072D)
	B, S, SS	26 - Black Oxide
	B, S	28 - Zinc Yellow (ASTM-B-633)

Tolerances
Unless otherwise Specified
.xxx +/-.005
.xx +/-.010
Angular +/- 1 Degree
Linear +/-.005
Break all sharp edges



This document is the property of Fascomp Inc. and shall not be reproduced, distributed, or used as a basis for manufacturing without written permission from Fascomp Inc.