

**CLI C 2-4 WS/SW 1 MP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

**General ordering data**

|                     |                                                                    |
|---------------------|--------------------------------------------------------------------|
| Version             | CableLine, Conductor and cable markers, 4 - 10 mm, 4 x 7 mm, white |
| Order No.           | <a href="#">0251310001</a>                                         |
| Type                | CLI C 2-4 WS/SW 1 MP                                               |
| GTIN (EAN)          | 4032248007967                                                      |
| Qty.                | 100 pc(s).                                                         |
| Alternative product | <a href="#">1568269999</a>                                         |

## CLI C 2-4 WS/SW 1 MP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 8 mm   | Depth (inches)  | 0.315 inch |
| Height     | 4 mm   | Height (inches) | 0.157 inch |
| Width      | 7 mm   | Width (inches)  | 0.276 inch |
| Net weight | 0.13 g |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

## General data

|                                              |                                                |                |
|----------------------------------------------|------------------------------------------------|----------------|
| Colour                                       | white                                          |                |
| Colour of printing                           | black                                          |                |
| Halogen                                      | Yes                                            |                |
| Insulation cross-section, max.               | 10                                             |                |
| Material                                     | PVC, soft, without Cadmium                     |                |
| Material colour according to resistance code | 9                                              |                |
| Number of markers per combination            | 1 Component part = Conductor and cable markers |                |
| Number of markers per packaging unit         | Form of supply                                 | Component part |
| Operating temperature range                  | -30...80 °C                                    |                |
| Operating temperature range, max.            | 80 °C                                          |                |
| Operating temperature range, min.            | -30 °C                                         |                |
| Orientation of print                         | horizontal                                     |                |
| Printed characters                           | Numbers                                        |                |
| Printing                                     | 1                                              |                |
| Printing method                              | hot-embossing                                  |                |
| Recommended industries                       | Process, Machinery                             |                |
| Type of printing                             | Standard                                       |                |
| UL 94 flammability rating                    | V-0                                            |                |
| Version                                      | MultiPack                                      |                |
| Width                                        | 7 mm                                           |                |

## Conductor and cable markers

|                               |                     |                                  |                          |
|-------------------------------|---------------------|----------------------------------|--------------------------|
| Conductor O.D.                | 4 - 10 mm           | Conductor O.D., max.             | 10 mm                    |
| Conductor O.D., min.          | 4 mm                | Conductor cross-section, max.    | 16 mm <sup>2</sup>       |
| Conductor cross-section, min. | 2.5 mm <sup>2</sup> | Cross-section for connected wire | 2.5 - 16 mm <sup>2</sup> |
| Halogen                       | Yes                 |                                  |                          |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |
| ECLASS 13.0 | 27-28-11-02 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

Creation date June 12, 2025 12:49:08 PM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.

## CLI C 2-4 WS/SW 1 MP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                             |                                                                      |
|-----------------------------|----------------------------------------------------------------------|
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                             |

### CLI C 2-4 WS/SW 1 MP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



Similar to illustration