


[Click here for the 3D model.](#)

### General Information

Series	T543 HRA
Dielectric	Polymer Tantalum
Style	SMD Chip
Description	SMD, Polymer, Molded, Up Screening
Features	Non-Combustible, Low ESR, High Reliability
RoHS	No
Prop 65	<b>WARNING:</b> Cancer and reproductive harm - <a href="https://www.p65warnings.ca.gov/">https://www.p65warnings.ca.gov/</a>
SCIP Number	b064b03e-bd75-42af-b342-1fe94dec2340
Termination	Tin Lead (SnPb)
AEC-Q200	No
Typical Component Weight	588.16 mg
Shelf Life	52 Weeks
MSL	3

### Dimensions

L	7.3mm +/-0.3mm	Capacitance	220 uF
W	4.3mm +/-0.3mm	Tolerance	10%
H	4mm +/-0.3mm	Voltage DC	16 VDC (105C), 10.72 VDC (125C)
T	0.13mm REF	Temperature Range	-55/+125°C
S	1.3mm +/-0.3mm	Rated Temperature	105°C
F	2.4mm +/-0.1mm	Humidity	60C, 90% RH, 500 Hours
A	3.8mm MIN	Dissipation Factor	10% 120Hz 25C
B	0.5mm +/-0.15mm	Failure Rate	N/A
E	3.5mm REF	ESR	35 mOhms (100kHz)
G	3.5mm REF	Ripple Current	2657 mA (rms, 100kHz 45C)
P	1.7mm REF	Leakage Current	352 uA (5min 25°C)
R	1mm REF	Testing and Reliability	10 Cycles Surge Current Testing At -55C +/-5C And +85C +/-5C
X	0.1mm +/-0.1mm REF		

### Packaging Specifications

Packaging	T&R, 178mm
Packaging Quantity	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.