

CLI C 3-6 GE/SW P MP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

Version	CableLine, Conductor and cable markers, 8 - 16 mm, 6 x 11 mm, yellow
Order No.	0253411667
Type	CLI C 3-6 GE/SW P MP
GTIN (EAN)	4008190100001
Qty.	20 pc(s).

CLI C 3-6 GE/SW P MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	17 mm	Depth (inches)	0.669 inch
Height	6 mm	Height (inches)	0.236 inch
Width	11 mm	Width (inches)	0.433 inch
Net weight	0.7 g		

Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

General data

Colour	yellow	
Colour of printing	black	
Halogen	Yes	
Insulation cross-section, max.	16	
Material	PVC, soft, without Cadmium	
Material colour according to resistance code	4	
Number of markers per combination	1 Component part = Conductor and cable markers	
Number of markers per packaging unit	Form of supply	Component part
Operating temperature range	-30...80 °C	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-30 °C	
Orientation of print	horizontal	
Printed characters	Upper-case letters	
Printing	P	
Printing method	hot-embossing	
Type of printing	Standard	
UL 94 flammability rating	V-0	
Version	MultiPack	
Width	11 mm	

Conductor and cable markers

Conductor O.D.	8 - 16 mm	Conductor O.D., max.	16 mm
Conductor O.D., min.	8 mm	Conductor cross-section, max.	70 mm ²
Conductor cross-section, min.	16 mm ²	Cross-section for connected wire	16 - 70 mm ²
Halogen	Yes		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02
ECLASS 13.0	27-28-11-02	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

CLI C 3-6 GE/SW P MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Downloads

Product Change Notification	PCN CableLine_DE PCN CableLine_EN
Catalogues	Catalogues in PDF-format

CLI C 3-6 GE/SW P MP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



Similar to illustration