



Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Drawing for packing(FREE)

Number of conductor:2, 3, 4, 5, 10, 12, 16, 18, 20




Style and dimension of reel (FREE)




Part No.	Code No.	F	G	H	J
DF53-2S-0.6H	CL0668-1001-0-00	7.5	16	17.4	21.4
DF53-3S-0.6H	CL0668-1002-0-00	7.5	16	17.4	21.4
DF53-4S-0.6H	CL0668-1003-0-00	7.5	16	17.4	21.4
DF53-5S-0.6H	CL0668-1004-0-00	7.5	16	17.4	21.4
DF53-10S-0.6H	CL0668-1007-0-00	11.5	24	25.4	29.4
DF53-12S-0.6H	CL0668-1008-0-00	11.5	24	25.4	29.4
DF53-16S-0.6H	CL0668-1010-0-00	11.5	24	25.4	29.4
DF53-18S-0.6H	CL0668-1011-0-00	11.5	24	25.4	29.4
DF53-20S-0.6H	CL0668-1012-0-00	11.5	24	25.4	29.4

5 Taping(FREE)



Reflow temperature profile in resistance to soldering heat




Number of reflow cycles 2 cycles MAX.

- Note
- 1 reel:5,000 connectors.
 - () is reference dimension.
 - Refer to IEC 60286-3 and JIS C 0806-3. (Packaging of components for automated handling)
 - This product satisfies halogen free requirements defined as 900 ppm maximum chlorine, 900 ppm maximum bromine, and 1500 ppm maximum total of chlorine and bromine.
 - Refer to the technical specification(ETAP-H1068) for packing type.
 - Please make sure refer to the manuals below for operation of this product.
For operation manual ETAD-H0996-00


HRS	DRAWING NO.	EDCX-402844-00-00
	PART NO.	DF53-S-0.6H
	CODE NO.	CL0010-0630-0-00
	NO.	2/3

Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Drawing for packing(FREE)
Number of conductor:6,8,14




Style and dimension of reel (FREE)




Part No.	Code No.	F	G	H	J
DF53-6S-0.6H	CL0668-1005-0-00	7.5	16	17.4	21.4
DF53-8S-0.6H	CL0668-1006-0-00	11.5	24	25.4	29.4
DF53-14S-0.6H	CL0668-1009-0-00	11.5	24	25.4	29.4

5 Taping (FREE)



Reflow temperature profile in resistance to soldering heat



Number of reflow cycles 2 cycles MAX.

- Note
- 1 reel:5,000 connectors.
 - () is reference dimension.
 - Refer to IEC 60286-3 and JIS C 0806-3. (Packaging of components for automated handling)
 - This product satisfies halogen free requirements defined as 900 ppm maximum chlorine, 900 ppm maximum bromine, and 1500 ppm maximum total of chlorine and bromine.
 - Refer to the technical specification(ETAP-H1068) for packing type.
 - Please make sure refer to the manuals below for operation of this product.
For operation manual ETAD-H0996-00

HRS	DRAWING NO.	EDCX-402844-00-00
	PART NO.	DF53-S-0.6H
	CODE NO.	CL0010-0630-0-00
	NO.	3