






Feb.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



PATTERN PROHIBITION AREA



RECOMMENDED PANEL CUOUT (SCALE 1/1)
 (PANEL THICKNESS : 1.6mm MAX)





HRS DRAWING FOR REFERENCE

NOTES ① PART No. ⑧ SHALL BE FINISHED AS TABLE SHOWN BELOW ACCORDING TO PANEL THICKNESS.
 (WASHER THICKNESS : 0.8)

② This product must be screwed to the board. Please prepare the screws by the customer.
 <SCREW REQUIREMENTS>
 NOMINAL DIAMETER: M3.5 x 0.6
 SCREW LENGTH : 2.4 ± 0.6 + BOARD thickness 't'

PANEL THICKNESS	NO. OF WASHER
t=0.7~1.0	2 EACH
t=1.5~1.8	1 EACH

5	ZINC ALLOY DIE CASTING	OVER: NICKEL PLATING 2#m min UNDER: COPPER PLATING 10#m min	8	STEEL	OVER: NICKEL PLATING 2#m min UNDER: COPPER PLATING 3#m min
4	PBT	UL94V-0(BLACK)	7	BRASS	OVER: NICKEL PLATING 2#m min UNDER: COPPER PLATING 1#m min
3	PBT	UL94V-0(BLACK)	6	STEEL	OVER: NICKEL PLATING 1#m min UNDER: COPPER PLATING 5#m min
1~2	PHOSPHOR BRONZE	CONTACT: GOLD PLATING 0.2#m min DIP: GOLD PLATING 0.03#m min UNDER: COPPER PLATING 2#m min			
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS



② PRODUCT - BOARD MOUNTED

UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	2	DIS-E-00010989	KG. OKITA	MN. KENJO	20220908
APPROVED : HO. MIWA			20050105	DRAWING NO. EDC3-040654-01		
CHECKED : YH. ENAMI			20050105	PART NO. DX20A-68S(50)		
DESIGNED : TU. TANIGUCHI			20050105	CODE NO. CL0230-0144-9-50		
DRAWN : TU. TANIGUCHI			20050105	②/1		