



Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Note ① Part No. ⑧ shall be finished as shown below according to panel thickness.

Panel thickness	Number of washer
t=0.7~1.0	2 each
t=1.5~1.8	1 each

② This product must be screwed to the board. Please prepare the screws by the customer.  
 <SCREW REQUIREMENTS>  
 NOMINAL DIAMETER: M3.5 x 0.6  
 SCREW LENGTH : 2.4 ± 0.6 + BOARD thickness 't'



NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
5	Zinc Alloy Die Casting	Over plating:Nickel 2µm min Under plating:Copper 10µm min	8	Steel	Over plating:Nickel 2µm min Under plating:Copper 3µm min
4	PBT	Black, UL94V-0	7	Brass	Over plating:Nickel 2µm min Under plating:Copper 1µm min
3	PBT	Black, UL94V-0	6	Steel	Over plating:Nickel 1µm min Under plating:Copper 5µm min
1~2	Phosphor Bronze	Contact area:Gold 0.2µm min Lead area:Gold 0.03µm min Under plating:Nickel 2µm min			

UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	2	DIS-E-00010989	KG. OKITA	MN. KENJO	20220908

APPROVED	CHECKED	DESIGNED	DRAWN	DRAWING NO.	PART NO.	CODE NO.
RI. TAKAYASU	AH. KODAMA	TS. ITO	AK. AKIYAMA	20180523	20180523	20180523
				EDC-043584-50-00		
				DX20A-80S(50)		
				CL0230-0158-3-50		1/1