






COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△△					△△				
△△					△△				



NOTE ① PART No. ⑩ SHALL BE FINISHED AS TABLE SHOWN BELOW ACCORDING TO PANEL THICKNESS: (WASHER THICKNESS : 0.8)

PANEL THICKNESS	No. OF WASHER
t=0.7~1.0	2 EACH
t=1.5~1.8	1 EACH

RECOMMENDED PANEL CUTOUT (SCALE FREE)



NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
6	STEEL	NICKEL PLATING	11	STEEL	NICKEL PLATING
5	PBT	UL94V-0(MILKY-WHITE)	10	STEEL	NICKEL PLATING
4	PHOSPHOR BRONZE	SELECTIVE GOLD PLATING 0.2μm	9	STEEL	NICKEL PLATING
3	PHOSPHOR BRONZE	SELECTIVE GOLD PLATING 0.2μm	8	PBT	UL94V-0(BLACK)
2	PHOSPHOR BRONZE	SELECTIVE GOLD PLATING 0.2μm	7	PBT	UL94V-0(BLACK)
1	PHOSPHOR BRONZE	SELECTIVE GOLD PLATING 0.2μm			

CODE NO. (OLD)	CL	DESIGNED	Y. Gami	CHECKED	H. Mura	APPROVED		RELEASED	
SCALE	1 : 1	DRAWN	J. Hanaga	DATE	03.10.27	APPROVED	03.10.09		
UNITS	mm								
DRAWING NO.	EDC3-042256-01	PART NO.	DX30A-100S-LNA(50)						
		CODE NO.	CL230-0168-7-50						

TO	
Q	