





Dec.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


ELV, RoHS COMPLIANT



NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM

NO. OF CYCLES : IR IN THE AIR OR NITROGEN
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C
60~120s

2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s
3. CO-PLANARITY : 0.1mm MAX
4. RECOMMENDED PCB THICKNESS : 1.6mm
5. RECOMMENDED SOLDER THICKNESS : 0.15mm



2	BRASS	TIN PLATED T=0.64	4	BRASS	TIN PLATED T=0.4
1	PPS	BLACK	3	BRASS	TIN PLATED T=0.64
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 2:1	COUNT 1	DESCRIPTION OF REVISIONS DIS-T-00023777	DESIGNED AN. SAIKI
APPROVED : AR. SHIRAI	2016. 07. 27	CHECKED : HS. OZAWA	2016. 07. 27	DESIGNED : TK. SHISHIKURA	2016. 07. 27
DRAWN : TK. SHISHIKURA	2016. 07. 27	APPROVED : AR. SHIRAI	2016. 07. 27	CHECKED : HS. OZAWA	2016. 07. 27
DESIGNED : TK. SHISHIKURA	2016. 07. 27	DRAWN : TK. SHISHIKURA	2016. 07. 27	DESIGNED : TK. SHISHIKURA	2016. 07. 27
DRAWN : TK. SHISHIKURA	2016. 07. 27	DESIGNED : TK. SHISHIKURA	2016. 07. 27	DRAWN : TK. SHISHIKURA	2016. 07. 27
EDC-360215-00-00	GT25H2-40DP-2. 2V	CL0775-0085-3-00	1	1	1

△ CAD Change