












ELV, RoHS COMPLIANT



PACKAGING SPECIFICATION



- NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.)  
 USED REFLOW SYSTEM : IR IN THE AIR OR NITROGEN  
 NO. OF CYCLES : 2 MAX  
 PEAK : 250°C  
 OVER 230°C : 20~40s  
 PREHEAT : 150~180°C  
 60~120s  
 2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s



3. CO-PLANARITY SHALL BE 0.1 MAX.  
 4. MARKING OF Lot No. : (EX)2009.6TH. SEPTEMBER → 09I06---5DIGITS  
 5. PC BOARD THICKNESS=1.6.  
 6. RECOMMENDED SOLDER THICKNESS=0.15  
 7. 1 REEL IS 450 CONECTORS.

2	BRASS	TIN PLATING			
1	PPS	BLACK	3	BRASS	TIN PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS	mm	SCALE	2 : 1	COUNT	DESCRIPTION OF REVISIONS
APPROVED : HH. TSUKUMO		20200321		DRAWING NO. EDC-167883-55-00	
CHECKED : HH. TSUKUMO		20200321		PART NO. GT8E-10P-2H(55)	
DESIGNED : DONGCHAN KIM		20200318		CODE NO. CL758-1007-0-55	
DRAWN : YK. MITSUISHI		20200318		DATE	

HRS DRAWING FOR REFERENCE

Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.