




Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes
- 1 Across flats hexagon head of REF. NO. ⑧: 1.27
The concave portion with REF. NO. ⑨ clamped to the cable.
The recommended tightening torque, REF. NO. ⑧: 0.3 to 0.4 N·m.
 - 2 The recommended tightening torque, REF. NO. ⑦: 2 to 2.5 N·m.
 - 3 LOCTITE 263, HENKEL JAPAN or equivalent applies to prevent REF. NO. ⑧ for loosening.
 - 4 LOCTITE 263, HENKEL JAPAN or equivalent applies to prevent REF. NO. ① for loosening.
 - 4 Applicable crimping tool of REF. NO. ⑨: HR10A-TC-03(CL150-0057-2)
 - 5 One example of the rotation of REF. NO. ⑦ to REF. NO. ① is shown.
 - 6 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure. Please confirm before the use.
 - 7 The assembly this product applies to the manual ETAD-C0354-00.

5	Brass	Matte finish nickel plated	10	Chloroprene rubber	(Black)
4	Brass	Gold plating 0.2μ min.	9	Brass	
3	Brass	Nickel under plating 2μ min.	8	Steel	Nickel plating M2.6×0.45×3
2	Polyamide	(Black) UL94V-0	7	Brass	Nickel plating
1	Zinc alloy	Matte finish nickel plated	6	Steel	Nickel plating
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 3	DESCRIPTION OF REVISIONS DIS-C-00016953	DESIGNED HT. ZENBA
		APPROVED : EJ. KUNII	20150929	DRAWING NO.	EDC-041593-74-74
		CHECKED : EJ. KUNII	20150929	PART NO.	HR10A-10PD-12P(74)
		DESIGNED : TP. KOMATSU	20150929	CODE NO.	CL0110-0448-0-74
		DRAWN : TP. KOMATSU	20150929		
					DATE 20240220