


Feb. 1. 2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES 1 APPLICABLE CRIMP CONTACT:
 HR12-SC-212(CL112-0480-9)
 APPLICABLE WIRE: AWG#26 TO #30
 (COVERED WIRE MAX. OUTSIDE DIA. ϕ 1)
 APPLICABLE CONTACT REMOVAL TOOL
 (EXTRACTION TOOL): HR12-SC-TP(CL150-0052-9)
 2 APPLICABLE CRIMPING TOOL OF REF. NO. 7:
 HR10A-TC-02(CL150-0041-2)
 THE HOLE DIAMETER FOR CRIMPING: ϕ 7.0
 3 THE RECOMMENDED CLAMP TORQUE, REF. NO. 5:
 : 2 TO 2.5 N·m.
 4 ACROSS FLATS HEXAGON HEAD OF REF. NO. 6: 1.27
 THE RECOMMENDED CLAMP TORQUE,
 REF. NO. 6: 0.3 TO 0.4 N·m.
 THE TIP OF REF. NO. 6 SHALL BE FIXED TO
 THE CONCAVE PORTION WITH REF. NO. 7 CLAMPED
 TO THE CABLE.
 5 LOCTITE 263, HENKEL JAPAN OR EQUIVALENT APPLIES
 TO PREVENT REF. NO. 1 AND 6 FOR LOOSENING.
 6 ONE EXAMPLE OF THE ROTATION OF REF. NO. 5 TO
 REF. NO. 1 IS SHOWN.
 7 THE CABLE PULL AND TWISTING STRENGTH AND
 OTHER CHARACTERISTICS MAY DIFFER,
 DEPENDING ON THE CABLE STRUCTURE.
 PLEASE CONFIRM BEFORE THE USE.
 8 THE ASSEMBLY THIS PRODUCT APPLIES TO
 THE MANUAL ETAD-C0354-00.

4	STEEL	NICKEL PLATING	8	CHLOROPRENE RUBBER	(BLACK)
3	BRASS	MATTE FINISH NICKEL PLATED	7	BRASS	
2	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0	6	STEEL	NICKEL PLATING M2.6X0.45X3
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	5	BRASS	NICKEL PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS	
				DIS-C-00017346	
				DESIGNED HT. ZENBA	CHECKED HY. KOBAYASHI
				DATE 20240508	
HIROSE ELECTRIC CO., LTD.		APPROVED :MO. SATOH	20070313	DRAWING NO. EDC4-026324-73	
		CHECKED :EJ. KUNII	20070312	PART NO. HR10A-10P-10SC(73)	
		DESIGNED :TO. HORII	20070309	CODE NO. CL0110-0602-9-73	
		DRAWN :MK. SATO	20070309	1/1	