


Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

1					2					3					4				
COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE				
△								△											
△								△											
△								△											



NOTE 1 APPLICABLE CRIMP CONTACT :
 HR10-PC-212(CL110-0514-3)
 (WIRE RENG:AWG#26 TO 30
 JACKET DIAMETER:φ 1 MAX)
 APPLICABLE CRIMP CONTACT
 EXTRACTION TOOL :
 RP6-SC-TP(CL150-0039-0)
 APPLICABLE CRIMP TOOL :
 HR10A-TC-02(CL150-0041-2)APPLY TO φ 7.

② THE RECOMMENDED CLAMP TORQUE, REF. NO. ④
 : 2 TO 2.5N · m.

③ ACROSS FLATS HEXAGON HEAD OF
 REF. NO. ⑤, ⑥ : 1.27.
 THE RECOMMENDED CLAMP TORQUE,
 REF. NO. ⑤, ⑥ : 0.3 TO 0.4N · m.

④ LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS
 RECOMMENDED TO PREVENT REF. NO. ①, ⑤, ⑥
 FOR LOOSENING.

5 ONE EXAMPLE OF THE ROTATION OF REF. NO. ④ TO
 REF. NO. ① IS SHOWN.

6 THE CABLE PULL AND TWISTING STRENGTH
 AND OTHER CHARACTERISTICS MAY DIFFER,
 DEPENDING ON THE CABLE STRUCTURE.
 PLEASE CONFIRM BEFORE THE USE.

4	BRASS	NICKEL PLATING	8	CHLOROPRENE RUBBER	(BLACK)
3	BRASS	NICKEL PLATING	7	BRASS	
2	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0	6	STEEL	NICKEL PLATING M2.6×0.45×3
1	BRASS	NICKEL PLATING	5	STEEL	NICKEL PLATING M2.6×0.45×2
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD) CL		DRAWN <i>M. Sato</i> 06.10.02	DESIGNED <i>T. Kematsu</i> 06.10.02	CHECKED <i>E. Kuna</i> 06.10.06	APPROVED <i>M. Sato</i> 06.10.06	RELEASED
DRAWING NO. EDC4-043234-73		PART NO. HR10A-10TP-12PC(73)				
SCALE 2 : 1		CODE NO. CL110-0455-6-73				1/1
UNITS mm		HRS HIROSE ELECTRIC CO., LTD.				

TO
R