

IE-KSF-PKV14M-KLROB-4.5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	
Order No.	1103660045
Type	IE-KSF-PKV14M-KLROB-4.5M
GTIN (EAN)	4050118359282
Qty.	1 pc(s).

IE-KSF-PKV14M-KLROB-4.5M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 0.01 g

Temperatures

Operating temperature -40 °C...70 °C

Electrical properties

Operating voltage 30 V

General standards

Connector standard IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14

Standards

Connector standard IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14

Cable structure

Sheath diameter, max.	9.3 mm	Sheathing colour	black (similar to RAL 9005)
-----------------------	--------	------------------	-----------------------------

Electrical properties of cable

Operating voltage 30 V

Mechanical and material properties of cable

Min. bending radius, once only	5 x cable diameter	Min. bending radius, repetitive	10 x cable diameter
--------------------------------	--------------------	---------------------------------	---------------------

Classifications

ETIM 6.0	EC001579	ETIM 7.0	EC001579
ETIM 8.0	EC001579	ETIM 9.0	EC001579
ETIM 10.0	EC001579	ECLASS 9.0	27-06-24-90
ECLASS 9.1	27-06-24-00	ECLASS 10.0	27-06-05-01
ECLASS 11.0	27-06-05-01	ECLASS 12.0	27-06-05-01
ECLASS 13.0	27-06-05-01	ECLASS 14.0	27-06-05-01
ECLASS 15.0	27-06-05-01		

Approvals

ROHS Conform

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

IE-KSF-PKV14M-KLROB-4.5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Downloads**


User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN

IE-KSF-PKV14M-KLROB-4.5M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Drawings



STECKANLEITUNG
RJ45

PAAR	LEITUNG	BEZUGSPUNKT
1	1 (BRN)	1
2	2 (BLU)	2
3	3 (GRN)	3
4	4 (ORN)	4
5	5 (BLK)	5
6	6 (BRN)	6
7	7 (GRN)	7
8	8 (BLK)	8