


Sep. 1. 2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



HRS DRAWING FOR REFERENCE

NOTES

- ① HAND CRIMPING TOOL. REF. NO. ⑧ : HR10A-TC-02 (CL150-0041-2)
- ② THE HOLE DIAMETER FOR CRIMPING: φ5.3
- ③ THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑥ : 1.5 TO 2 N·m.
- ④ ACROSS FLATS HEXAGON HEAD OF REF. NO. ⑦ : 1.27 THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑦ : 0.3 TO 0.4N·m.
- ⑤ THE TIP OF REF. NO. ⑦ SHALL BE FIXED TO THE CONCAVE PORTION WITH REF. NO. ⑧ CLAMPED TO THE CABLE.
- ⑥ LOCTITE 263, HENKEL JAPAN OR EQUIVALENT APPLIES TO PREVENT REF. NO. ① AND ⑦ FOR LOOSENING.
- ⑦ ONE EXAMPLE OF THE ROTATION OF REF. NO. ⑥ TO REF. NO. ① IS SHOWN.
- ⑧ THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE. PLEASE CONFIRM BEFORE THE USE.
- ⑨ THE ASSEMBLY THIS PRODUCT APPLIES TO THE MANUAL ETAD-C0354-00.

4	BRASS	MATTE FINISH NICKEL PLATED	9	CHLOROPRENE RUBBER	(BLACK)
3	PHOSPHOR BRONZE	OVER PLATING: GOLD 0.2μm min. UNDER PLATING: NICKEL 2μm min.	8	BRASS	
2	POLYAMIDE	(BLACK) UL94V-0	7	STEEL	NICKEL PLATING M2.6X0.45X2
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	6	BRASS	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00016958	DESIGNED HT. ZENBA	CHECKED EJ. KUNII	DATE 20240227
HRS HIROSE ELECTRIC CO., LTD. APPROVED : MO. SATOH 20070307 CHECKED : MO. SATOH 20070307 DESIGNED : TO. HORII 20070307 DRAWN : MK. SATO 20070307				DRAWING NO. EDC4-020535-74 PART NO. HR10A-7P-4S(74) CODE NO. CL0110-0302-5-74			