



1	2	3	4						
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
1	1	1	1	1	1	1	1	1	1
2	2	2	2	2	2	2	2	2	2
3	3	3	3	3	3	3	3	3	3
4	4	4	4	4	4	4	4	4	4


A A




PANEL CUTOUT  
( $t = 0.7 \text{ TO } 2$ )



1  
2  
4 ATTACHED  
2 5 ATTACHED  
3 PRESS FITTING



$\phi 11 \pm 0.3$   
 $\phi 8.85 \pm 0.2$   
 $12.2 \pm 0.5$   
 $6.45 \pm 0.3$   
M8 x 0.5



(1.5)  
(0.55)  
(10) HEX

A DETAIL OF MOUNTING GUIDE

NOTES 1 APPLICABLE CRIMP CONTACT:HR10-PC-212(CL110-0514-3)  
APPLICABLE WIRE:AWG#26 TO #30(COVERED WIRE MAX,OUTSIDE DIA. $\phi 1$ )  
APPLICABLE CONTACT REMOVAL TOOL(EXTRACTION TOOL):RP6-SC-TP(CL150-0039-0)  
2 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑤ TO BE 1.5 N·m.  
LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO  
PREVENT REF. NO. ⑤ FROM LOOSENING.

NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS	
3	POLYBUTYLENE TEREPHTHALATE (BLACK)	UL94V-0	5	BRASS	NICKEL PLATING	
2	STAINLESS STEEL		4	PHOSPHOR BRONZE	NICKEL PLATING	
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED				
CODE NO.(OLD) CL		DRAWN <i>M. Sato</i>	DESIGNED <i>J. Kozai</i>	CHECKED <i>E. Kuni</i>	APPROVED <i>M. Sato</i>	RELEASED
		07.04.11	07.04.11	07.04.11	07.04.11	

F

TO	DRAWING NO.	PART NO.	CODE NO.	1
R	EDC4-042729-73	HR10G-7R-6PC(73)	CL110-1706-0-73	1
	SCALE 2 : 1 UNITS mm			1
	HIROSE			1