




1			2			3			4		
COUNT	DESCRIPTION OF REVISIONS		BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS		BY	CHKD	DATE
1			.	.	.	1			.	.	.
2			.	.	.	2			.	.	.
3			.	.	.	3			.	.	.
4			.	.	.	4			.	.	.

A A







PANEL CUTOUT
($t = 0.7$ TO 2)




1
2
4 ATTACHED
5 ATTACHED
3 PRESS FITTING





(1.5)
(10) HEX



A DETAIL OF MOUNTING GUIDE

D D

E E

F F

NOTES 1 APPLICABLE CRIMP CONTACT:HR12-SC-212(CL112-0408-9)
APPLICABLE WIRE:AWG#26 TO #30(COVERED WIRE MAX,OUTSIDE DIA. ϕ 1)
APPLICABLE CONTACT REMOVAL TOOL(EXTRACTION TOOL):HR12-SC-TP(CL150-0050-3)
2 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑤ TO BE 1.5 N·m.
LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO
PREVENT REF. NO. ⑤ FROM LOOSENING.

NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS		
3	POLYBUTYLENE TEREPHTHALATE (BLACK)	UL94V-0	5	BRASS	NICKEL PLATING		
2	STAINLESS STEEL		4	PHOSPHOR BRONZE	NICKEL PLATING		
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED					
CODE NO.(OLD) CL			DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
			<i>A. Sato</i> 07.04.11	<i>J. Hwang</i> 07.04.11	<i>E. Kurni</i> 07.04.11	<i>M. Sato</i> 07.04.11	
F			DRAWING NO. EDC4-042728-73		PART NO. HR10G-7R-6SC(73)		
F			SCALE 2 : 1		CODE NO. CL110-1705-7-7-3		
F			UNITS mm		1 1		

1 2 3 4

HIROSE ELECTRIC CO., LTD.