

A

2

3

4

A


B

C



D

F

F



CONTACT ARRANGEMENTS VIEWED FROM THE MATING SIDE



NOTES  1 THE RECOMMENDED CLAMP TORQUE, REF. NO. ④ AND ⑩ : 1.5 N·m.
 2 THREAD LOCKER TO THE THREADED PORTION OF REF. NO. ①
APPLIES TO PREVENT REF. NO. ④ FROM LOOSING.
RECOMMENDED THREAD LOCKER:LOCTITE 263, HENKEL JAPAN LTD.
REF. NO. ⑩ SHALL BE TIGHTENED BY TORQUE AFTER
CLAMPED UNTIL IT TOUCHES THE SURFACE B.
 3 ONE EXAMPLE OF THE ROTATION OF REF. NO. ①, ④ AND ⑩ ARE SHOWN.
 4 THE ASSEMBLY THIS PRODUCT APPLIES TO THE MANUAL ETAD-C0355-00.

5	POLYAMIDE					
4	BRASS	MATTE FINISH NICKEL PLATED	10	BRASS	MATTE FINISH NICKEL PLATED	
3	BERYLLIUM COPPER	GOLD PLATING 0.2μm min.	9	POLYAMIDE		
		NICKEL UNDER PLATING 2μm min.	8	BRASS	MATTE FINISH NICKEL PLATED	
2	POLYAMIDE	(BLUE)	7	STEEL	NICKEL PLATING	
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	6	STAINLESS STEEL		
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS	
UNITS mm	SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-C-00016940	DESIGNED HT. ZENBA	CHECKED EJ. KUNII	DATE 20240214
F HRS HIROSE ELECTRIC CO., LTD.	APPROVED : MO. SATOH		20051024	DRAWING NO.	EDC4-007759-73	
	CHECKED : EJ. KUNII		20051021	PART NO.	HR10-7P-6S(73)	
	DESIGNED : DS. MATSUNE		20051019	CODE NO.	CL0110-0024-4-73	
	DRAWN : DS. MATSUNE		20051019			11