


Dec.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
1. ONE EXAMPLE OF THE ROTATION OF REF. NO. 7, 8 AND REF. NO. 1 IS SHOWN.
 2. THE RECOMMENDED CLAMP TORQUE REF. NO. 8 : 3 TO 4 N · m.
LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. 8 FROM LOOSENING.
 3. THE RECOMMENDED CLAMP TORQUE REF. NO. 11 : 0.2 TO 0.3 N · m.
LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. 11 FROM LOOSENING.
 4. THIS PRODUCT TO BE USED WITH CABLECLAMP, JR13WCC-*(72). THE RECOMMENDED CLAMP TORQUE : 3 TO 4 N · m. AND LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT FROM LOOSENING. * DESIGNATE DIAMETER OF APPLICABLE CABLE.
 5. THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE. PLEASE CONFIRM BEFORE THE USE.

NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
6	PHOSPHOR BRONZE	NICKEL PLATING			
5	STEEL	NICKEL PLATING	11	STAINLESS STEEL	JISB1177 HEAGON SOCKET SET SCREW M2.6X0.45
4	BRASS	NICKEL PLATING	10	ACRYLONITRILE BUTADIENE RUBBER	(BLACK)
3	ACRYLONITRILE BUTADIENE RUBBER	(BLACK)	9	PHOSPHOR BRONZE	NICKEL PLATING
2	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0	8	BRASS	NICKEL PLATING
1	ZINC ALLOY	NICKEL PLATING	7	BRASS	NICKEL PLATING

UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	△				
APPROVED : HY. KOBAYASHI			18.02.22	DRAWING NO. EDC-116688-31-00		
CHECKED : HY. KOBAYASHI			18.02.22	PART NO. HR22-12WTLP-20PC(31)		
DESIGNED : HY. KISHI			18.02.21	CODE NO. CL122-0064-9-31		
DRAWN : MK. INOUE			18.02.06	△ 1/1		