



Feb.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



NOTES 1 APPLICABLE CRIMP CONTACT:HR22-PC-222(CL122-0009-0)  
 ※APPLICABLE WIRE:AWG#24 TO 28, JACKET DIAMETER:φ1.15(MAX)  
 APPLICABLE CONTACT REMOVAL TOOL(EXTRACTION TOOL):RP6-SC-TP(CL150-0039-0)  
 2 THE RECOMMENDED CLAMP TORQUE, REF. NO. 5 : 2 TO 3N · m.  
 AND LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT FROM LOOSENING.

3	Silicone rubber	(Black)					
2	Polybutylene terephthalate	(Black)	UL94V-0	5	Brass	Nickel plating	
1	Zinc alloy	Nickel plating		4	Brass	Nickel plating	
NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH	REMARKS
UNITS	mm	SCALE	2 : 1	COUNT	1	DESCRIPTION OF REVISIONS	DIS-C-00020593
		DESIGNED	HY. KISHI	CHECKED	HY. KOBAYASHI	DATE	20250813
APPROVED : E.J. KUNII				20160213	DRAWING NO. EDC-042800-73-00		
CHECKED : E.J. KUNII				20160213	PART NO. HR22-12WTRA-20PC(73)		
DESIGNED : S.J. SHIMIZU				20160213	CODE NO. CL0122-0005-0-73		
DRAWN : S.J. SHIMIZU				20160213	1/1		