







Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

1 2 3 4 5 6 7 8

A
B
C
D
E
F



3 FIG.1



HRS DRAWING FOR REFERENCE

- NOTES 1 THIS PRODUCT IS APPLY TO THE WIRE AWG#30(WIRE JACKET DIAMETER ϕ 0.71 MAX).
 2 PER PACK : 100 CONTACTS.
 3 RECOMMEND CABLE PREPARATION DIMENTION ARE SHOWN IN FIG.1.
 4 APPLICABLE OPERATION CRIMP TOOL:HR25-TA3032HC

NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
			1	PHOSPHER BRONZE	CONTACT AREA: GOLD 0.2 μ m min. TERMINAL AREA:NICKEL PLATING 1 μ m min. UNDER PLATING : NICKEL PLATING 1 μ m min.

UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	10:1	△				
HIROSE ELECTRIC CO., LTD.			APPROVED : E.J. KUNII	15.10.05	DRAWING NO. EDC-110401-00-00	
			CHECKED : E.J. KUNII	15.10.05	PART NO. HR25-SC-111	
			DESIGNED : WR. AJIRO	15.10.05	CODE NO. CL125-0421-3-00	
			DRAWN : WR. AJIRO	15.10.05	1/1	

FORM HC0011-5-7 1 2 3 4 5 6 7 8