




- Notes
- 1 Total length becomes 28.8 ± 1 when Ref.No. ⑥ is screwed into Ref.No. ① completely.
 - 2 The recommended clump torque of Ref.No. ⑥ to be $0.45 \sim 0.5 \text{ N} \cdot \text{m}$.
To prevent loosening, apply LOCTITE 263 and LOCK PRIMER 7649 manufactured by HENKEL JAPAN Co., Ltd. according to the Loctite Coating Procedure Manual (ETAD-C0151-00).
Spacer for assembly is available HR30-6P-T02.
 - 3 Table for assembly and soldering is available HR30-6R-6P-T01.
 - 4 Surface plating : gold plating $0.2 \mu\text{m}$ min.
Under plating : nickel plating $2 \mu\text{m}$ min.
 - 5 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure.
Please confirm before the use.
 - 6 The assembly this product applies to the manual ETAD-C0476-00.

3	PPS	(Black) UL94V-0	6	PBT	(Black) UL94V-0
2	Brass	4	5	CR	(Black)
1	PPS	(Black) UL94V-0	4	Polyacetal	(Natural)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 5 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00014969	DESIGNED HY. KISHI
		APPROVED : MR. YOSHIDA	20050105	DRAWING NO.	EDC3-112570-71
		CHECKED : MO. SATOH	20050105	PART NO.	HR30-6JA-6P(71)
		DESIGNED : YH. YAMADA	20050105	CODE NO.	CL0130-2018-7-71
		DRAWN : YH. YAMADA	20050105		
		DATE	20230404	CHECKED	HY. KOBAYASHI