


Feb.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes
- ① Contact area: gold plating 0.2 μm min.
Lead area: gold plating flash.
Under plating: nickel 2 μm min.
 - ② The recommended clamp torque of Ref.No. ⑦ to be 0.8N · m.
LOCTITE 263, LOCPRIMER 7649, HENKEL JAPAN is recommended to prevent Ref.No. ⑦ from loosening.
 - ③ After Ref.No. ⑤ is inserted to Ref.No. ①, Ref.No. ① is mounted on the panel.
Make sure that Ref.No. ⑤ does not have any factors to reduce water-resistancy, such as scratch, twist, pinching, or dust.
 - 4 Table for soldering is available HR30-7J-12PC-T01.
 - 5 The assembly of this product applies to the manual ETAD-C0302-00

△ CAD change

4	Polyphenylen sulfide	(Black) UL94V-0					
3	Copper alloy	①	7	Brass	Nickel plating		
2	Copper alloy	①	6	Phosphor bronze	Nickel plating		
1	Polyphenylen sulfide	(Black) UL94V-0	5	Chloroprene rubber	(Black)		
NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH	REMARKS
UNITS	mm		SCALE	5:1	COUNT	3	1
DESCRIPTION OF REVISIONS			DESIGNED	CHECKED	DATE		
DIS-C-00016206			HY. KISHI	HY. KOBAYASHI	2023. 09. 27		
APPROVED : HY. KOBAYASHI 2018. 02. 26			DRAWING NO.		EDC-113453-31-00		
CHECKED : HY. KOBAYASHI 2018. 02. 26			PART NO.		HR30-7R-12P (31)		
DESIGNED : DS. MATSUNE 2018. 02. 24			CODE NO.		CL0130-1016-6-31		
DRAWN : AI. NISHIYAMA 2018. 02. 22					1/1		