

1	2	3	4	5	6	7	8																						
A	A	A	A	A	A	A	A																						
				<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 12.5%;">COUNT</td> <td style="width: 12.5%;">DESCRIPTION OF REVISIONS</td> <td style="width: 12.5%;">BY</td> <td style="width: 12.5%;">CHKD</td> <td style="width: 12.5%;">DATE</td> <td style="width: 12.5%;">COUNT</td> <td style="width: 12.5%;">DESCRIPTION OF REVISIONS</td> <td style="width: 12.5%;">BY</td> <td style="width: 12.5%;">CHKD</td> <td style="width: 12.5%;">DATE</td> </tr> <tr> <td>5</td> <td>..</td> <td>..</td> <td>..</td> <td>..</td> <td>5</td> <td>..</td> <td>..</td> <td>..</td> <td>..</td> </tr> </table>				COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	5	5		
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE																				
5	5																				
B	B	B	B	B	B	B	B																						
C	C	C	C	C	C	C	C																						
D	D	D	D	D	D	D	D																						
E	E	E	E	E	E	E	E																						
F	F	F	F	F	F	F	F																						
<p>NOTES</p> <p>① PLATING(REF.NO.③, ④) CONTACT AREA : GOLD 0.2μ m min OTHERS : GOLD AND NICKEL UNDER PLATING : NICKEL 2μ m min</p> <p>② THE RECOMMENDED CLAMP TORQUE OF REF.NO.⑧ TO BE 2 TO 2.5N·m. THREAD LOCKER TO THE THREADED PORTION OF REF.NO.① IS RECOMMENDED TO PREVENT REF.NO.⑧ FROM LOOSING. RECOMMENDED THREAD LOCKER:LOCTITE 271, HENKEL JAPAN LTD.</p> <p>③ WHEN THIS CONNECTOR IS MOUNTED ON TO PANEL, BE CAREFUL REF.NO.⑥ IS ASSEMBLED SURELY INTO THE GROOVE OF REF.NO.⑥ AS SHOWN IN THIS FIGURE TO KEEP WATERPROOF EFFECTIVENESS.</p>				<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 33.3%;">CODE NO. (OLD) CL</td> <td style="width: 33.3%;">DRAWN k.abe</td> <td style="width: 33.3%;">DESIGNED H.Zemba</td> </tr> <tr> <td colspan="2"></td> <td>CHECKED M.Sato</td> </tr> <tr> <td colspan="2"></td> <td>APPROVED M.yoshida</td> </tr> <tr> <td colspan="2"></td> <td>RELEASED 05.05.16</td> </tr> </table> <table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 12.5%;">SCALE 4 : 1</td> <td style="width: 12.5%;">UNITS mm</td> <td style="width: 12.5%;">DRAWING NO. EDC3-114398</td> <td style="width: 12.5%;">PART NO. LF13WBR-20P</td> </tr> </table> <table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 12.5%;">CODE NO. CL</td> <td style="width: 12.5%;">DRAWING NO. EDC3-114398</td> <td style="width: 12.5%;">PART NO. LF13WBR-20P</td> </tr> <tr> <td colspan="2"></td> <td>CODE NO. CL136-1009-9</td> </tr> </table>				CODE NO. (OLD) CL	DRAWN k.abe	DESIGNED H.Zemba			CHECKED M.Sato			APPROVED M.yoshida			RELEASED 05.05.16	SCALE 4 : 1	UNITS mm	DRAWING NO. EDC3-114398	PART NO. LF13WBR-20P	CODE NO. CL	DRAWING NO. EDC3-114398	PART NO. LF13WBR-20P			CODE NO. CL136-1009-9
CODE NO. (OLD) CL	DRAWN k.abe	DESIGNED H.Zemba																											
		CHECKED M.Sato																											
		APPROVED M.yoshida																											
		RELEASED 05.05.16																											
SCALE 4 : 1	UNITS mm	DRAWING NO. EDC3-114398	PART NO. LF13WBR-20P																										
CODE NO. CL	DRAWING NO. EDC3-114398	PART NO. LF13WBR-20P																											
		CODE NO. CL136-1009-9																											