





Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Note:
1. Applicable wire is UL3266 AWG#18-#22. Insulation diameter $\phi 2.1$ mm max.
 2. Per reel : 6000 contacts.
 3. Applicable crimping machine and crimping conditions (crimp height etc.) will be specified according to AWG # or wire applied.
 4. Refer to ATA1-E3143 for crimp quality standards.

NO.	MATERIAL	FINISH . REMARKS
1	Copper alloy	Contact area : gold plating min. $0.2\mu\text{m}$ Terminal area : tin plating min. $0.5\mu\text{m}$ Others: nickel plating min. $0.5\mu\text{m}$

UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	5 : 1	△				
HIROSE ELECTRIC CO., LTD.			APPROVED : AH. KODAMA 15.07.21 CHECKED : AH. KODAMA 15.07.21 DESIGNED : KI. KAGOTANI 15.07.21 DRAWN : KI. KAGOTANI 15.07.21	DRAWING NO. EDC-128588-00-00 PART NO. MT50B-1822PCFA CODE NO. CL248-0005-0-00		