



△ (Language change)

Panel cutout  
t=0.5 to 2



Note 1 The recommended tightening torque of ref. No. ⑤ shall be 3 to 4 N·m.  
LOCTITE 243, HENKEL JAPAN or equivalent is recommended to prevent  
ref. No. ⑤ from loosening.

|                                                                                                                     |                                                                                     |                         |                                                                                                                                                                             |                                  |                          |                              |            |               |          |
|---------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------|--------------------------|------------------------------|------------|---------------|----------|
| 3                                                                                                                   | PPS                                                                                 | (BLACK) UL94V-0         |                                                                                                                                                                             | 6                                | PHOSPHOR BRONZE          | NICKEL PLATING               |            |               |          |
| 2                                                                                                                   | COPPER ALLOY                                                                        | SILVER PLATING 2μm min. |                                                                                                                                                                             | 5                                | BRASS                    | NICKEL PLATING               |            |               |          |
| 1                                                                                                                   | BRASS                                                                               | NICKEL PLATING          |                                                                                                                                                                             | 4                                | PPS                      | (BLACK) UL94V-0              |            |               |          |
| NO.                                                                                                                 | MATERIAL                                                                            | FINISH . REMARKS        |                                                                                                                                                                             | NO.                              | MATERIAL                 | FINISH . REMARKS             |            |               |          |
| UNITS<br>mm                                                                                                         |  | SCALE<br>2 : 1          |                                                                                          | COUNT                            | DESCRIPTION OF REVISIONS |                              | DESIGNED   | CHECKED       | DATE     |
|                                                                                                                     |                                                                                     |                         |                                                                                                                                                                             | 1                                | DIS-C-00007408           |                              | TY. SUZUKI | HY. KOBAYASHI | 20210802 |
|                                                                                                                     |                                                                                     |                         |                                                                                                                                                                             | APPROVED : SU. OBARA 20150924    |                          | DRAWING NO. EDC-027794-81-00 |            |               |          |
|                                                                                                                     |                                                                                     |                         |                                                                                                                                                                             | CHECKED : HY. KOBAYASHI 20150924 |                          | PART NO. RM15TRH-4SA(81)     |            |               |          |
|                                                                                                                     |                                                                                     |                         |                                                                                                                                                                             | DESIGNED : KN. IKEHARA 20150924  |                          | CODE NO. CL0109-0848-9-81    |            |               |          |
|  HIROSE<br>ELECTRIC<br>CO., LTD. | DRAWN : KN. IKEHARA 20150924                                                        |                         |   |                                  |                          |                              |            |               |          |