


Jan.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



HRS DRAWING FOR REFERENCE

- Notes 1 Applicable crimp contact:
RP13A-PC-222/CL113-0141-7
(Applicable cable size : awg#24 to #28.
Cable jacket outer diameter shall be
φ1.4mm or less.)
- 2 Applicable cable crimping tool :
RP13A-TC-01/CL150-0070-0
- 3 Extraction tool :
RP13-PC-TP/CL150-0021-5
- ④ The tightening torque of Ref No. ⑥ :
0.15 to 0.2 N·m.
To prevent loosening Ref No. ⑥ , use
LOCTITE 243, HENKEL JAPAN or equivalent.
- 5 Shall be disassembled when delivered.
- ③ 6 The cable pull and twisting strength and
other characteristics may differ, depending
on the cable structure, please confirm
before the use.

3	Polycarbonate	UL94V-0 (BLACK)	6	Brass	Black chromete treatment (Trivalent chromium) JIS B 1111 M2X0.4X4
2	Polycarbonate	UL94V-0 (BLACK)	5	Polyvinylchloride	(BLACK)
1	Polycarbonate	UL94V-0 (BLACK)	4	Brass	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT ③ 4	DESCRIPTION OF REVISIONS DIS-C-00009777	DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI	DATE 20220209
HRS HIROSE ELECTRIC CO., LTD.	APPROVED : MO. SATOH	20051116	DRAWING NO.	EDC4-009601-71			
	CHECKED : HT. ZENBA	20051116	PART NO.	RP13A-12J-13PC(71)			
	DESIGNED : EM. YUMINO	20051110	CODE NO.	CL0113-0166-8-71	③	1	1
	DRAWN : EM. YUMINO	20051110					