




Relays & Contactors > Electromechanical Relays > Standard Signal Relay 2 Form C,2 CO Cont



Relay & Contactor Type: **General Purpose Signal Relay**
Coil Magnetic System: **Polarized, Monostable**
Contact Arrangement: **2 Form C DPDT-CO**
Current Type: **DC**
Contact Current Rating: **2 A**

[All Standard Signal Relay 2 Form C,2 CO Cont \(72\)](#)

Features

Product Type Features

Relay & Contactor Type	General Purpose Signal Relay
------------------------	------------------------------

Configuration Features

Contact Special Features	Bifurcated/Twin Contacts
Relay Options	Power Switching, RF Rated
Contact Number of Poles	2
Contact Arrangement	2 Form C DPDT-CO

Electrical Characteristics

Contact Limiting Short-Time Current	2 A
Contact Limiting Making Current	2 A
Contact Limiting Continuous Current	2 A
Contact Limiting Breaking Current	2 A
Insulation Initial Dielectric Between Open Contacts	750 Vrms
Insulation Initial Dielectric Between Adjacent Contacts	1000 Vrms



Contact Switching Voltage (Max)	250 VAC
Contact Switching Load (Min)	.1mA @ .0001V
Voltage Standing Wave Ration (HF Parameter)	1.06db @ 100MHz, 1.49db @ 900MHz
Coil Resistance	145 Ω
Insulation Initial Resistance	1000000 M Ω
Contact Current Rating	2 A
Coil Voltage Rating	4.5 VDC
Contact Voltage Rating	220 VDC
Coil Power Rating DC	.14 W
Insulation Initial Dielectric Between Contacts & Coil	1800 Vrms

Signal Characteristics

Isolation (HF Parameter)	-18.8dB @ 900MHz, -37dB @ 100MHz
Insertion Loss (HF Parameter)	-.03dB @ 100MHz, -.33dB @ 900MHz

Body Features

Product Weight	.75 g[.026 oz]
Enclosure Type	Hermetically Sealed

Contact Features

Contact Plating Material	Gold
Contact Material	PdRu

Termination Features

Main Termination & Connection Type	Solder Pins
Coil Termination & Connection Type	Solder Pins

Mechanical Attachment

Product Mount Type	Board Mount
--------------------	-------------

Dimensions

Product Width	6 mm[.236 in]
Product Length	10 mm[.393 in]
Product Height	5.65 mm[.222 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
Environmental Category of Protection	RTV
Environmental Ambient Temperature (Max)	85 °C[185 °F]



Operation/Application

Solder Process	Wave Solder Capable
Coil Magnetic System	Polarized, Monostable
Current Type	DC

Packaging Features

Packaging Method	Tube
------------------	------

Other

Coil Power Rating Class	≤.15 W
Contact Current Class	≤2 A
Height Class (Mechanical)	≤7 mm[≤.276 in]
Length Class (Mechanical)	≤11 mm[≤.433 in]
Width Class (Mechanical)	≤7 mm[≤.276 in]

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts




TE Part # 6-1462039-4
IM02KS=IM RELAY 140mW 4.5V short pins



TE Part # 2-1462039-8
IM22TS=IM RELAY 50mW 4.5V


Also in the Series | Axicom IM



DC Relays(142)




Electromechanical Relays(142)




General Purpose Signal Relays(142)


Customers Also Bought




TE Part #815702-SF
RN212-4-02-0M7



TE Part #280370-2
2P AMPMODU II SHRD HDR, ST, 0.38 AU




TE Part #280372-2
6P AMPMODU II SHRD HDR, ST, 0.38 AU



TE Part #280520-2
12P AMPMODU II SHRD HDR, ST, 0.38 AU



TE Part #3-1462039-0
IM23TS=IM RELAY 50mW 5V



TE Part #1-1586037-2
12P VERT HDR VAL-U-LOK V2



TE Part #3-1623930-4
CFR25 5% 1K8



TE Part #1625867-2
RP 1J 0.166W 10K 0.1% 25PPM 1K RL



TE Part #5-2176230-6
3522 33K 5% 3W



TE Part #5646492-1
2MM HM,ASY,T-F,REC,TT/PRE-SHLD

Documents

Product Drawings

IM02TS=IM RELAY 140mW 4.5V

English

CAD Files

Customer View Model

ENG_CVM_1462037-4_A7.3d_igs.zip

English

Customer View Model

ENG_CVM_1462037-4_A7.3d_stp.zip

English

Customer View Model

ENG_CVM_1462037-4_A7.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_CVM_1-1462037-3_B4.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1462037-3_B4.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1-1462037-3_B4.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Transportation, Storage, Handling, Assembly and Testing of Axicom Through Hole Terminal (THT) Relays

English

IM_Datasheet

English



Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

VDE Certificate

English