

**IE-C5DD4UG0200A2EXXX-X**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



**General ordering data**

Version	Dragline cable, PROFINET, RJ45 IP 67 PushPull V14 metal, Open, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PUR, 20 m
Order No.	<a href="#">1203620200</a>
Type	IE-C5DD4UG0200A2EXXX-X
GTIN (EAN)	4050118062328
Qty.	1 pc(s).

## IE-C5DD4UG0200A2EXXX-X

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Length	20 m	Length (inches)	787.402 inch
Net weight	1,240 g		

## Temperatures

Storage temperature	-50 °C...70 °C	Operating temperature	-40 °C...70 °C
Installation temperature	-20 °C...60 °C		

## Cable specific standards

Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)	Standard, shielding material	DIN EN 13602 Cu-ETP-A..B
Standard, wire material	DIN EN 13602 Cu-ETP-A		

## Cable structure

Arrangement of wire cores	Star-quad	Colour sequence or wires - wire pairs	white, yellow, blue, orange
Complete shielding	Aluminium foil, Shielding braid made from copper wiring	Cross-section	4*AWG 22/7 - 0.32 mm <sup>2</sup>
Diameter of inner sheathing	3.9 mm	Filler	As central element
Insulation	PE	Insulation cross-section	1.5 mm
Material sheath	PUR	Number of wires	4
Overlap of shielding braid	85 %	Sheath diameter, max.	6.7 mm
Sheath diameter, min.	6.3 mm	Sheathing colour	green (RAL 6018)
Sheathing material thickness	0.9 mm	Shielding	SF/UTP
Shielding braid thickness	0.13 mm	Standard designations	2YH(ST)C11Y 2x2x0.75/1.5-100 LI VZN GN FRNC
Strands	7	Wire core insulation thickness	0.38 mm
Wire material	Stranded tin-plated copper wire		

## Electrical properties of cable

Capacity at 1 kHz	52 nF/km	Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)
Characteristic impedance	100 ± 15 Ω at 1-100 MHz	Delay skew	40 ns/100m
Loop resistance	120 Ω/km	Operating voltage (UL rating)	600 V
Operating voltage, UL	600 V	Resistance differential	3 %
Signal propagation time	5.3 ns/m	Speed	180 m/min
Test voltage: wire-wire-shield	2000 V <sub>eff</sub> , 50 Hz, 1 min	Transfer impedance	20 mΩ/m at 10 MHz

## Mechanical and material properties of cable

Abrasion resistance	very good	Acceleration	4 m/s <sup>2</sup>
Bending cycles	3 Mio	Fire propagation	No
Halogen	halogen-free, according to IEC 60754-2	Min. bending radius, once only	5 x cable diameter
Min. bending radius, repetitive	7.5 x cable diameter	Pulling force	≤ 150 N
Resistance to oils	in accordance with IEC 60811-2-1	Resistance to spread of flame	in accordance with IEC 60332-1
Silicone-free	Yes	Speed	180 m/min
UV-resistant	Yes		

Creation date June 13, 2025 5:30:29 AM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.

2

**Data sheet**

**IE-C5DD4UG0200A2EXXX-X**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Plug**

Plug left	RJ45, IP67, male contact, straight, PushPull V14, plug, Plastic, shielded	Plug right	free conductor end
-----------	---	------------	--------------------

**Plug, left**

Plug left	RJ45, IP67, male contact, straight, PushPull V14, plug, Plastic, shielded
-----------	---

**Plug, right**

Plug right	free conductor end
------------	--------------------

**Classifications**

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 9.0	27-06-03-08
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-08
ECLASS 11.0	27-06-03-08	ECLASS 12.0	27-06-03-08
ECLASS 13.0	27-06-03-08	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

**Approvals**

Approvals



Approvals MAMID	<a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/</a>
-----------------	---

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>