

## VP M32 EXE MS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Similar to illustration



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Version	VPMS Ex (ex blanking plug, brass), Blanking plug, straight, M 32, 12 mm, Brass, nickel-plated
Order No.	<a href="#">1210920000</a>
Type	VP M32 EXE MS
GTIN (EAN)	4032248992409
Qty.	10 pc(s).
Delivery status	<b>This article will no longer be available in the future.</b>
Available until	2024-08-31
Alternative product	<a href="#">1218970000</a>

Creation date June 14, 2025 7:32:11 PM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.

## VP M32 EXE MS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	16 mm	Height (inches)	0.63 inch
Length	16 mm	Length (inches)	0.63 inch
Diameter	32 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	11 mm	Net weight	86.1 g

## Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

## Certificate numbers cable gland

Certificate no. cable gland (ATEX)	INERIS 09 ATEX 0059X	Identification	II 2 GD, Ex d IIC, Ex e II, Ex tD
------------------------------------	----------------------	----------------	-----------------------------------

## General information

AF size 1	39 mm	Diameter of sealing ring	32 mm
External thread	M 32	Halogen	Yes
Length of thread	12 mm	Material	Brass, nickel-plated
O-Ring	NBR	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Protection degree	IP54, IP64, IP68	Silicone	No
Torque for cap nut, max.	10.8 Nm	Torque for cap nut, min.	7.2 Nm
Torque for connecting adapter, max.	36 Nm	Torque for connecting adapter, min.	18 Nm

## Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 9.0	27-14-44-25
ECLASS 9.1	27-14-44-35	ECLASS 10.0	27-14-44-25
ECLASS 11.0	27-14-44-25	ECLASS 12.0	27-14-08-05
ECLASS 13.0	27-14-08-05	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1 Imidazolidine-2-thione 96-45-7
SCIP	4efa9808-c72a-4b94-8dcb-498465ba8c6e

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**

**VP M32 EXE MS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

