

Wire Protection &amp; Management &gt; Interconnect Devices &gt; SolderSleeve Shield Terminators

Operating Temperature (Max): **125 °C [ 257 °F ]**Expanded Inside Diameter (Min): **10.8 mm [.425 in ]**Recovered Inside Diameter (Max): **4.5 mm [.177 in ]**Pre-Installed Lead: **No**Resistance Properties: **Splash Protection**

## Features

### Product Type Features

Temperature Indicator	No
-----------------------	----

### Configuration Features

Pre-Installed Lead	No
--------------------	----

### Dimensions

Compatible Jacket Diameter Range	10.7 mm[.42 in]
Product Length	35.5 mm[1.4 in]
Shield Outside Diameter (Min)	7.1 mm[.28 in]
Expanded Inside Diameter (Min)	10.8 mm[.425 in]
Recovered Inside Diameter (Max)	4.5 mm[.177 in]

### Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Resistance Properties	Splash Protection
Wire Temperature (Max)	85 °C

### Industry Standards

Government Qualified	No
MIL/NAS Specification (MIL-S-83519, NAS-1747)	No

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (.32% in Solder) Cd (.18% in Solder) <b>Article Safe Usage Statements:</b> Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts





## Also in the Series | RAYCHEM CWT



SolderSleeve Shield Terminators(24)

## Customers Also Bought

TE Part #222963-000  
B-150-17TE Part #5068104006  
CGPT-19/9.5-2-SPTE Part #4036954002  
CGPT-1.5/0.5-0-SPTE Part #272423-000  
CWT-9TE Part #5038814001  
DCPT-10/5-45-SPTE Part #A95650-000  
HX-SCE-1K-9.5-50-4TE Part #CAT-T3437-D1  
D-SCE Fluid Resistant SleevesTE Part #718157-000  
B-150-33TE Part #8244994001  
ZH-100-3/16-0-SP

## Documents

### Product Drawings

#### CWT-11

English

### Datasheets & Catalog Pages

#### 1654025\_Sec8\_B-155\_CWT\_D-110\_D-1744

English

### Product Specifications

[SolderSleeve One-Step Wire and Cable Terminators Installation Procedures for CWT and B-155 Products](#)

English

[Product Specification](#)

English