

Cable Assemblies > RF Cable Assemblies



Cable Assembly (End A): UMCC GEN 2 Plug

Cable Assembly (End B): UMCC GEN 4 Plug

Cable Assembly Length: .17 m [.55 ft]

Coax Cable Type: .81mm Coax

Impedance: 50 Ω

Features

Product Type Features

Cable Assembly (End A)	UMCC GEN 2 Plug
Cable Assembly (End B)	UMCC GEN 4 Plug
Coax Cable Type	.81mm Coax
Cable Assembly Type	UMCC2 to UMCC4

Configuration Features

Number of Connectorized Ends	2
------------------------------	---

Electrical Characteristics

Insulation Resistance	300 MΩ
Operating Voltage	15 V
Impedance	50 Ω

Signal Characteristics

Velocity of Propagation	70 %
-------------------------	------

Body Features

Body Plating Material	Gold
Conductor Material	Copper
Strain Relief Type	Heat Shrink Tubing
Conductor Plating Material	Gold
Jacket Material	FEP
Cable Color	Black

Contact Features

Ferrule Material	Brass
------------------	-------

Dimensions

Outside Cable Diameter	.81 mm [.031 in]
Wire Size	36 AWG

Usage Conditions

Operating Temperature Range	-40 – 85 °C [-40 – 185 °F]
-----------------------------	----------------------------

Operation/Application

Operating Frequency Range	9 GHz
---------------------------	-------

Other

Dielectric Material	FEP
Cable Assembly Length	.17 m [.55 ft]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1909763-1
UMCC MICRO-COAX RECPT GEN 1
HIGHER LEVEL




TE Part # 2334884-1
UMCC Micro-Coax receptacle, Gen 4



TE Part # 2337019-1
UMCC Micro-Coax receptacle, Gen 1

Also in the Series | UMCC



Coax Connectors(3)



RF Cable Assemblies(95)

Customers Also Bought



TE Part #ADP-SMAM-SMAM
SMA Plug to SMA Plug




TE Part #CONMHF4-SMD-G-T
MHF4 Jack 50 Ohm PCB Surface Mount



TE Part #1-1623729-8
BCHE 17 W 3K3 5%



TE Part #2-1624113-9
3650 0805 10nH 5% 2K RL



TE Part #5-1775444-2
EMIX CONN., 1.5MM PITCH, HDR, R/A, 2P



TE Part #2015357-3
C/A, UMCC/UMCC, 1.37 OD CABLE,
100MM LON



TE Part #2015699-1
RF CA,UMCC GEN1-GEN1,0.81MM
CABLE,L100MM



TE Part #2-2176345-6
CRGCQ 1210 1K2 1%



TE Part #2199230-3
M.2 0.5PITCH 4.2H KEY B 15U" AU



TE Part #2201778-1
MICRO SD PUSH PUSH LOW PROFILE
TYPE

Documents

Product Drawings

[RF CA,UMCC GEN2-GEN4,0.81,L50,BLACK](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2016677-3_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2016677-3_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2016677-3_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

English