



Automotive Parts > Automotive Connector Accessories > Other Automotive Connector Accessories



Primary Product Color: **Black**

Primary Product Material: **PBT GF**

Automotive Connector Accessory Type: **Cover**

Operating Temperature Range: **-40 – 120 °C, -40 – 105 °C [-40 – 221 °F, -40 – 248 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Cover
-------------------------------------	-------

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF

Usage Conditions

Operating Temperature Range	-40 – 120 °C, -40 – 105 °C[-40 – 221 °F][-40 – 248 °F]
-----------------------------	--

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC




Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2371101-1 MATENET INLINE COUPLER ASSY, COD A	 TE Part # 2302450-1 MATENET, FEMALE INSERT MODUL, BLACK	 TE Part # 2320201-1 1-PORT MATENET HDR ASSY, 90DEG, COD A	 TE Part # 2420634-1 HYBRID,PLUG HSG ASSY,UNSEALED, COD A
 TE Part # 2305390-1 5-PORT MATENET HDR ASSY 90DEG, COD A	 TE Part # 2304372-1 1-PORT MATENET HDR ASSY 90DEG, COD A	 TE Part # 4-2302461-1 MATENET INLINE COUPLER, ASSY, COD A	 TE Part # 2308956-1 1-PORT MATENET HDR ASSY 180DEG, COD A

Customers Also Bought

 TE Part #2236905-1 NANO TAB 0.5X0.4,TERMINAL	 TE Part #2289592-2 SEAL COVER, 180 DEGREE, FAKRA	 TE Part #2302450-1 MATENET, FEMALE INSERT MODUL, BLACK	 TE Part #2307194-2 1POS,FAKRA AUT,SOC INNER HSG, SLD,180 DEG
---	---	---	---



Documents

Product Drawings

1-PORT MATENET FRAME,STP, COD A

German

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2302510-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2302510-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2302510-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English