

2306498-1

✓ ACTIVE

MATE-AX

TE Internal #: 2306498-1

Cable-to-Cable, 180° Cable Exit, 2 Position, A Code, Housing for Male Terminals, 4 mm [.157 in] Centerline, Crimp, Data Connectivity Housings

[View on TE.com >](#)

Automotive Parts > Automotive Connectors > Data Connectivity Housings



Connector System: **Cable-to-Cable**

Sealable: **No**

Cable Exit Angle: **180°**

Number of Positions: **2**

Connector & Keying Code: **A**

Features**Product Type Features**

Primary Locking Feature	On the Terminal
Connector & Contact Terminates To	Wire & Cable
Mixed & Hybrid Connector	No
Connector System	Cable-to-Cable
Sealable	No
Connector & Housing Type	Housing for Male Terminals

Configuration Features

Number of Rows	1
Number of Positions	2

Body Features

Body Material	PA66 GF30
Cable Exit Angle	180°
Connector & Keying Code	A

Contact Features

Mating Pin Diameter	.4 mm [.016 in]
---------------------	-----------------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Housing Color	Jet Black
---------------	-----------

Centerline (Pitch)	4 mm [.157 in]
--------------------	----------------

Dimensions

Product Width	25.7 mm [1.012 in]
---------------	--------------------

Product Length	12 mm [.472 in]
----------------	-----------------

Connector Height	10.75 mm [.423 in]
------------------	--------------------

Usage Conditions

Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C [221 °F]
-----------------------------	---

Cable Type	RTK 031
------------	---------

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Shielded	No
----------	----

Other

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250)
--	--

Candidate List Declared Against: JAN 2025 (247)

Does not contain REACH SVHC

Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
-----------------	--

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2298125-1
MATE-AX, Pin center contact, RTK 031



TE Part # 2298126-1
MATE-AX, Crimp Ferrule, RTK 031



TE Part # 2318197-1
MATE-AX,RF-ADAPTER,2P SOC,RPC 3.50 SOC



TE Part # 2306868-1
2P,MATE-AX,SOC HSG ASSY COD A



TE Part # 2298123-1
MATE-AX, Pin outer contact, RTK 031



TE Part # 2298508-1
MATE-AX, Pin center contact, RG 174



TE Part # 2298509-1
MATE-AX, Crimp Ferrule, RG 174




TE Part # 2298506-1
MATE-AX, Pin outer contact, RG 174



TE Part # 2-2306868-1
2POS,MATE-AX,PIN HSG ASSY,SLD, COD A,180

Customers Also Bought



Documents

Product Drawings

2 P, MATE-AX,PIN HSG, COD A

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2306498-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2306498-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2306498-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English