

Wire Protection & Management > Heat Shrink Shapes > Bushings & Bobbins



Material Systems Code: 200

Product Width: 25 mm [.98 in]

Molded Part Type: Bobbins

Primary Product Material: Modified Fluoro-Elastomer

Flexibility: Flexible

Features

Product Type Features

Molded Part Type	Bobbins
------------------	---------

Configuration Features

Adhesive Requirement	Adhesive Purchased Separately
----------------------	-------------------------------

Body Features

Primary Product Color	Black
-----------------------	-------

Material Code	12
---------------	----

Material Systems Code	200
-----------------------	-----

Primary Product Material	Modified Fluoro-Elastomer
--------------------------	---------------------------

Flexibility	Flexible
-------------	----------

Dimensions

Product Width	25 mm [.98 in]
---------------	----------------

Expanded Inside Diameter (Min)	39 mm [1.54 in]
--------------------------------	-----------------

Recovered Inside Diameter (Max)	12.7 mm [.5 in]
---------------------------------	-----------------

Usage Conditions

Operating Temperature Range	-67 – 392 °C
-----------------------------	--------------

Other

Adhesive Code	S1255-04
---------------	----------

Size Code	12
-----------	----

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability






Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought

TE Part #026831-000
202W302-25-0TE Part #ZPF000000000001237
097-0179-16TE Part #ZPF000000000001224
097-0104-16TE Part #329047-000
210W321-25-0TE Part #5960044018
TFER-3/8-X-SPTE Part #159189-000
263W023-25-0TE Part #395415-000
202W331-25-0TE Part #323749
DIAMOND GRIP 12-10 HT R 8TE Part #323751
DIAMOND GRIP 12-10 HT R 1/4TE Part #ZPF000000000009314
984-6SE 22-55 SN-L

Documents

Product Drawings

202W312-12-0

English

Datasheets & Catalog Pages

1654025_Sec4_-12

English

Raychem Molded Parts Visual Guide

English