

10606-26-9

✓ ACTIVE


RAYCHEM

TE Internal #: 390231-000

75 ohm, 26 AWG, -65 – 200 °C [-85 – 392 °F], High Speed Digital & Data Cable

[View on TE.com >](#)

Wire & Cable > High Speed Digital & Data Cable

Cable Type: **Cheminax**Impedance: **75 Ω**Wire Size: **26 AWG**Operating Temperature Range: **-65 – 200 °C [-85 – 392 °F]**

Features

Product Type Features

Cable Style	Twisted Pair
-------------	--------------

Electrical Characteristics

Capacitance	.00003 pF/m[30 pF/ft]
-------------	-----------------------

Impedance	75 Ω
-----------	------

Body Features

Jacket Material	Radiation-Crosslinked, Modified ETFE
-----------------	--------------------------------------

Conductor Material	Silver-Plated High Strength Copper
--------------------	------------------------------------

Cable Color	White
-------------	-------

Shield Plating Material	Tin
-------------------------	-----

Shield Material	Copper
-----------------	--------

Dimensions

Outside Cable Diameter	2.82 mm[.111 in]
------------------------	------------------

Cable Dielectric Diameter	.99 mm[.039 in]
---------------------------	-----------------

Conductor Diameter Range	.53 mm[.021 in]
--------------------------	-----------------

Wire Size	26 AWG
-----------	--------

Usage Conditions

Cable Type	Cheminax
------------	----------

Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]
-----------------------------	----------------------------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 449453-000
D-150-0708-5

Customers Also Bought



Documents

[Product Specifications](#)

[Product Specification](#)

English