




Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **MIL Spec, TE Product Specification (114-)**
TE Certification: **Yes – Certificate Included**
Power Technology Type: **Battery, Electric, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Electric, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-P592-R472A PIDG Ring Tongue Terminals	 TE Part # 2-130102-1 PG 16-14 RING M5, TAPE	 TE Part # CAT-P592-SH816 PIDG Short Spring Spade Tongue Terminals	 TE Part # 52956 TERMINAL,PG SPR SPD 16-14 8
 TE Part # 53244-1 TERMINAL,PG SPR SPD 16-14 8	 TE Part # 53874-1 TERMINAL,PG SPD FLG 16-14 8	 TE Part # 52955-1 TERMINAL,PG SPR SPD 16-14 6	 TE Part # CAT-P592-T116 PIDG Pre-Insulated Diamond Grip Tabs
 TE Part # 31899 TERMINAL,PIDG R 16-14 8	 TE Part # 32447 KNIFE DISCONNECT,PIDG 16-14	 TE Part # 32957 TERMINAL,PG R 16-14 6	 TE Part # 34164 TERMINAL,PG R 16-14 3/8





TE Part # 34165
TERMINAL,PG SPD 16-14 6



TE Part # 32441
TERMINAL,PIDG R 16-14 4



TE Part # 326741
TERMINAL,PG SPD 16-14 8



TE Part # 34898
TERMINAL,PG RECT 16-14 6



TE Part # 34159
TERMINAL,PG R 16-14 6



TE Part # 324227
PG SHUR PLUG 16-14



TE Part # 34160
TERMINAL,PG R 16-14 8



TE Part # 66024-2
TAB,PIDG TERMI-BK 16-14

Customers Also Bought



TE Part #1-1393243-0
RTE24024

Documents

Datasheets & Catalog Pages

Bottoming Dies

English

Instruction Sheets

C-Head Adapter Battery Powered Crimp Tool Kit, PN 2844990-[]

C-Head Adapter Battery Powered Crimp Tool Kit, PN 2844990-[]

C-Head Adapter Battery Powered Crimp Tool Kit, PN 2844990-[]

German

C-Head Adapter Battery Powered Crimp Tool Kit, PN 2844990-[]

French

C-Head Adapter Battery Powered Crimp Tool Kit, PN 2844990-[]

C-Head Adapter Battery Powered Crimp Tool Kit, PN 2844990-[]

English