



Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**
Insertion & Extraction Tool Application: **Contact-to-Housing**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Housing

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 7-927852-3
POS-LOCK STECKH 6,3

TE Part # 172076-5
POSITIVE LOCK 250 HOUSING RECEPTACLE

TE Part # 7-927852-5
POS-LOCK STECKH 6,3

TE Part # 7-927852-4
POS-LOCK STECKH 6,3

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(177)

Insulation Boots & Sleeves(5)

Magnet Wire Terminals(1)

PCB Terminals(133)

Quick Disconnects(172)

Splices(4)

Also in the Series | Positive Lock 250

Automotive Terminals(1)

Crimp Terminal Housings(177)

Insertion & Extraction Tools(3)

Insulation Boots & Sleeves(5)



[Quick Disconnects\(172\)](#)

Customers Also Bought



TE Part #63850-1
[187 FASTON REC 20-16 AWG NPST](#)




TE Part #280756-2
[FF 375 REC 3-6MM2 TPBR](#)



TE Part #1-480702-0
[04P UMNL PLUG HSG NATL](#)



TE Part #521205-7
[RAST 5, P-L mk3 HSG.-3 POS \(sp](#)



TE Part #603502-3
[PRE-INSUL SEALED SPLICE 22-16](#)



TE Part #926298-7
[UNIVERSAL MATE-N-LOK 4 WAY PLUG](#)



TE Part #927833-2
[SPT REC 6.3 Contact SRC Sn](#)



TE Part #6368150-1
[MJ,TE,8P,CAT5,SHIELDED](#)

TE Part #2-1999828-3
[PLATE, GAUGE](#)

TE Part #2294711-1
[BLOCK, PUSHER 38P](#)

Documents

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English

[Instruction Sheet \(non U.S.\)](#)

Japanese

[AMP EXTRACTION TOOL P/N724659-1/-2/-5 FOR EXTRACTING POSITIVE LOCK CONNECTOR CONTACTS INSTRUCTION SHEET](#)

English



AMP EXTRACTION TOOL P/N724659-1/-2/-5 FOR EXTRACTING POSITIVE LOCK CONNECTOR CONTACTS INSTRUCTION SHEET

Japanese