


Wire Protection & Management > Heat Shrink Shapes > Heat Shrink Boots > Bulbous Heat Shrink Boots: Lipped, Straight



Body Orientation: **Straight**

Molded Part Shape Code: **202**

Lipped: **Yes**

Material Code: **4**

Material Systems Code: **10**

[All Bulbous Heat Shrink Boots: Lipped, Straight \(358\)](#)

## Features

### Configuration Features

Lipped	Yes
Adhesive Requirement	Adhesive Purchased Separately

### Body Features

Primary Product Material	Polyolefin Flexible Modified
Material Code	4
Material Systems Code	10

### Housing Features

Body Orientation	Straight
------------------	----------

### Dimensions

Compatible Cable Diameter (Max)	6 mm, 7 mm, 8 mm, 9 mm, 10 mm, 11 mm[.23 in][.27 in][.314 in][.35 in][.39 in][.43 in]
Compatible Cable Diameter Range	5.6 – 12.4 mm[.22 – .488 in]

### Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
Resistance Protection	Occasional Fluid Exposure

### Industry Standards

Compatible With Approved Standards Products	SAE AS I 81765/1, Type II, UL 224, File
---	---

E85381

**Other**

Molded Part Shape Code	202
------------------------	-----


**Product Compliance**

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**

TE Part # 890060-000  
S1017-1.0X50


**Customers Also Bought**



TE Part #718759-000  
44AM1121-22-9/96-9CS2275



TE Part #095226-000  
S1030-TAPE-3/4X33FT



TE Part #806089-000  
202C642-71-0



TE Part #024639-000  
202D142-4/86-0



TE Part #2008625-1  
Socket Micro MNL, TIN 22-18 AW



TE Part #CAT-M1-R4491  
M12 Right Angle Crimped Strain Relief



TE Part #1-2823582-6  
POSITIONER M12 RAIL A8 STANDARD



TE Part #ES4100402ATM  
ES4100402ATM=RELAY



TE Part #ES2100402ATM  
ES2100402ATM=RELAY

## Documents

### Product Drawings

202D121-4-0

English

---

### Datasheets & Catalog Pages

1654025\_Sec4\_-4

English

[Raychem Molded Parts Visual Guide](#)

English

---

### Product Specifications

[Product Specification](#)

English