



HTCM-SCE-TP

TE Internal #: E61464-000
High Temperature, -55 – 225 °C [-67 – 437 °F], White, HTCM-SCE-TP, Printable Tags
[View on TE.com >](#)

Identification & Labeling > Printable Tags > High Temperature Markers, HTCM-SCE-TP



Printable Tag Grade: **High Temperature**
Operating Temperature Range: **-55 – 225 °C [-67 – 437 °F]**
Primary Product Color: **White**

[All High Temperature Markers, HTCM-SCE-TP \(8\)](#)

Features

Product Type Features

Printable Tag Grade	High Temperature
---------------------	------------------

Body Features

Primary Product Color	White
-----------------------	-------

Mechanical Attachment

Number of Tie-Wrap Holes	6
--------------------------	---

Dimensions

Product Length	50.8 mm[2 in]
Product Height	12.7 mm[.5 in]

Usage Conditions

Operating Temperature Range	-55 – 225 °C[-67 – 437 °F]
-----------------------------	----------------------------

Printer/Label Features


Printer Technology	Thermal Transfer
--------------------	------------------

Packaging Features

Packaging Quantity	250
--------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)






EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 2-160968-2
CABLE TY 134X2.6 BLACK




TE Part # 2-160968-1
FOAC CABLE TY NATURAL 134X2.6



TE Part # 4-160971-2
CABLE TY 140X3.6 BLACK




TE Part # 2-160971-2
FOAC CABLE TY BLACK 140X3.6




TE Part # 754073-000
TMS-RJS-RIBBON-4HT






TE Part # 4-160996-2
CABLE TY 200X3.6 BLA



TE Part # 4-160968-1
CABLE TY 134X2.6 NAT



TE Part # 1-2186501-1
T3212-SWARE-PRINTER




TE Part # 2-160977-2
CABLE TY 290X4.8 BLA




TE Part # 2-160978-2
CABLE TY 360X4,8BLA



TE Part # 2-100715-1
CABLE TY 150X3,6NAT




TE Part # 2-160975-1
CABLE TY 200X4.8 NAT




TE Part # 4-160970-1
CABLE TY 200X2.6 NAT



TE Part # 4-160975-1
CABLE TY 200X4.8 NAT



TE Part # 4-160975-2
CABLE TY 200X4.8 BLA




TE Part # 4-160968-2
CABLE TY 134X2.6 BLACK

Also in the Series | HTCM-SCE-TP



Printable Tags(6)

Customers Also Bought




TE Part #3823083001
44A1131-16-0/2/9-9



TE Part #118577-000
S01-05-R




TE Part #775210-000
S01-03-R



TE Part #CAT-AS22759-34
SAE AS22759: 34/35/41/42/43 - Dual-Wall, Normal Weight Wire



TE Part #ZPF000000000136664
182-0908-20



TE Part #689127-000
202D211-25/225-0



TE Part #F99802-000
S200-3-W1-22-9



TE Part #61316-1
FF 250 TAB 22-18AWG TPBR



TE Part #926897-1
UNIV.M-N-L.PIN

Documents

Product Drawings

HTCM-SCE-TP-1/2-6H-9

English

Datasheets & Catalog Pages

HTCM-SCE-TP Thermal Transfer Cable Marker

English

IDENTIFICATION SELECTION GUIDE

English

Cable Identification Product Shelf Life

English

Product Specifications

CABLE MARKER INSTALLATION GUIDE

English