



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	18	PRODUCTION ISSUE	11NOV2025	AR	ME

a) Part as supplied.



b) Part after unrestricted recovery.



DIMENSIONS in millimetres [in inches, for reference] ? See over for explanation of Notes ① and ②

Part No.	H		J		P	R	S	T	U&V	JO	HW	JW	X	Y
	Min a	Max b	Min a	Max b	±10% b	±10% b	±10% b	±10% b	±10% b	±10% b	±20% b	±20% b	±20% b	±20% b
① 202K121	24 [.94]	10.4 [.41]	24 [.94]	5.6 [.22]	38 [1.50]	21 [.83]	3.0 [.12]	1.0 [.04]	12 [.47]	8.5 [.33]	1.6 [.06]	0.9 [.04]	24 [.94]	13 [.51]
① 202K132	30 [1.18]	14.2 [.56]	30 [1.18]	5.9 [.23]	55 [2.17]	32 [1.26]	3.0 [.12]	1.0 [.04]	12 [.47]	11.5 [.45]	1.8 [.07]	1.0 [.04]	24 [.94]	18 [.71]
① 202K142	31 [1.22]	18.0 [.71]	31 [1.22]	7.1 [.28]	67 [2.64]	35 [1.38]	3.0 [.12]	1.0 [.04]	20 [.79]	17.0 [.67]	1.8 [.07]	1.0 [.04]	32 [1.26]	25 [.98]
① 202K153	36 [1.42]	22.4 [.88]	36 [1.42]	8.4 [.33]	80 [3.15]	42 [1.65]	3.0 [.12]	1.0 [.04]	20 [.79]	19.5 [.77]	2.0 [.08]	1.0 [.04]	32 [1.26]	30 [1.18]
202K163	43 [1.69]	28.2 [1.11]	43 [1.69]	9.9 [.39]	99 [3.90]	61 [2.40]	3.0 [.12]	1.7 [.07]	20 [.79]	21.0 [.83]	2.2 [.09]	1.2 [.05]	52 [2.05]	30 [1.18]
202K174	60 [2.36]	35.1 [1.38]	60 [2.36]	15.7 [.62]	130 [5.12]	72 [2.83]	3.0 [.12]	1.7 [.07]	20 [.79]	39.0 [1.54]	3.2 [.13]	1.5 [.06]	52 [2.05]	50 [1.97]
202K185	66 [2.60]	44.5 [1.75]	66 [2.60]	16.8 [.66]	170 [6.69]	90 [3.54]	3.0 [.12]	2.0 [.08]	20 [.79]	51.5 [2.03]	3.8 [.15]	2.0 [.08]	52 [2.05]	70 [2.76]

RELEASED FOR PUBLICATION


ALL RIGHTS RESERVED.

TE Connectivity Ltd.

COPYRIGHT



THIS DRAWING IS UNPUBLISHED.

DIMENSIONS:		DWN	April 2007		MATERIAL		SEE SHEET 2		FINISH						
mm [INCHES]		A.LILLEY.			—										
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	—		 TE Connectivity Ltd.										
		APVD	—												
		PRODUCT SPEC			NAME										
		—													
APPLICATION SPEC			—												
—															
0 PLC	± —	WEIGHT		SIZE	CAGE CODE	DRAWING NO			RESTRICTED TO						
1 PLC	± —			A4	00779	C-202K1XX-XX-0			—						
2 PLC	± —														
3 PLC	± —														
4 PLC	± —														
ANGLES	± —	CUSTOMER DRAWING													
		SCALE				DNS		SHEET		1 of 2		REV		18	

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATIBILITY CHART

Material Dash Number	Material Description	SPEC Number	Coating Slash Number
—3	POLYOLEFIN, SEMI-RIGID	RT-301	/42, /86, /180
—4	POLYOLEFIN, FLEXIBLE	RT-1304	/42, /86, /180
—25	ELASTOMER, FLUID RESISTANT	RW-2070	/42, /86, /225

Ordering Information

202K1**-*—/**—0

COLOR DESIGNATOR

Adhesive Slash Number (if required see compatibility chart)

Material Dash Number (see compatibility chart)

Base Part Number

NOTES

- Supplied with 2 lips only, Dimension V does not apply.
- Potting Port X @ 90° to Potting Port Y on 202K121.
- If eyelet clip (000W212) is required with part then add CS-1858 to description (i.e. 202K132-3-CS-1858-0).
- As supplied dimensions are for uncoated parts, when coating is added entry diameters will reduce by 1.5mm[.06] Max.
- Potting Ports with plug and riser are optional, when specified by suffix -00 they will be located as shown.
- On some parts a bump or depression at the material injection point may exist as a normal manufacturing process.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - TE Connectivity Ltd.

DIMENSIONS: mm [INCHES]	DWN A.LILLEY.	April 2007	MATERIAL —	FINISH —			
	CHK —	—	 TE Connectivity Ltd.				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD —	—					
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	PRODUCT SPEC —	NAME BOOT, STRAIGHT WITH LIP —					
	APPLICATION SPEC —	SIZE A4	CAGE CODE 00779	DRAWING NO C-202K1XX-XX-0	RESTRICTED TO —		
	WEIGHT	CUSTOMER DRAWING			SCALE DNS	SHEET 2 OF 2	REV 18

