


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A	GTP		11JUN2023	ED	WH



CONN 1  
FEMALE STR  
CODE Z WATER BLUE  
WITH CLIP SLOT  
SEALED


CONN 2  
FEMALE STR  
CODE Z WATER BLUE  
WITH CLIP SLOT  
SEALED

TE P/N	L(mm)	REV
2081390-1	300+10/-0	A
2081390-2	600+10/-0	A
2081390-3	1000+15/-0	A
2081390-4	2000+20/-0	A
2081390-5	3000+30/-0	A
2081390-6	5000+40/-0	A

NOTES:

- ALL RF CONNECTORS MUST BE ASSEMBLED PER MANUFACTURER'S APPLICATION SPECIFICATIONS WITH FOLLOWING [SC]:  
1.1: SOCKET CONTACTS CRIMP HEIGHT  
1.2: FERRULES' CRIMP HEIGHT  
1.3: CONNECTORS TO COAX CABLE RETENTION FORCE
- 100% IN-PROCESS ELECTRICAL TEST:  
2.1: DC CONTINUITY, FOR CENTER AND OUTER CONDUCTORS, POINT TO POINT  
2.2: SHORT CIRCUITS;
- TEMPERATURE RANGE: -40°C TO 85°C

4. LABEL CONTENT:



AR	MM	DESCRIPTION	QTY	ITEM
		TEAR TAPE FOR PACKAGING	10	
1	PC	ID LABEL	9	
AR	MM	DAR462 COAXIAL CABLE	8	
2	PC	SEAL COVER	7	
2	PC	WIRE SEAL	6	
2	PC	OUTER FERRULE	5	
2	PC	SUBASSY FEMALE	4	
2	PC	CENTER CONTACT FEMALE	3	
2	PC	INNER HOUSING SUBASSEMBLY	2	
2	PC	FAKRA HSG FEMALE 1P CODE Z	1	
-X	U/M	DESCRIPTION		ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Z.Z.ZHONG 23FEB2023	TE Connectivity	
DIMENSIONS: mm		CHK ERIC.DAI 23FEB2023	NAME -	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD WENKE.HE 23FEB2023	PRODUCT SPEC -	
MATERIAL -		FINISH -	WEIGHT -	RESTRICTED TO -
		APPLICATION SPEC -	SIZE A2	CAGE CODE 00779
			DRAWING NO C=2081390	SCALE -
		CUSTOMER DRAWING	SHEET 1 of 1	REV A