





P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	27JUN2025	C JH	TD
	A1	REVISED PER ECR-25-251883	04AUG2025	C JH	TD



LOOSE PIECE CONFIGURATION
4-2980010-()



TERMINALS TO UNWIND FROM REELS AS SHOWN
2980010-()



- 1 SPECIFICATION
UPPER SLOT 18-22AWG LEAD WIRE OR DIODE WIRE REFER TO
MPG06G 0.584-0.635mm. MUR260 0.70-0.90mm.
LOWER SLOT 0.16-1.02mm MAGNET COPPER WIRE

2 POCKET RECOMMENDATION: DRAWING 2980012

- 3 TERMINAL APPLICATION TO COMPLY WITH TE CONNECTIVITY SPECIFICATION 114-13166, FIG. 4

2980010-2
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CHUNJIE	23NOV2023	TE Connectivity NAME MULTIPLE WIRE TO WIRE, SIAMEZE TERMINAL			
DIMENSIONS: mm		CHK JUSTIN	23NOV2023				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD TIM DING	23NOV2023				
0 PLC ± 1 PLC ±0.25 2 PLC ±0.15 3 PLC ± 4 PLC ± ANGLES ±2°		PRODUCT SPEC 108-161572	APPLICATION SPEC - 3				
MATERIAL BRASS SPRING HARD	FINISH - POST TIN	WEIGHT -	CUSTOMER DRAWING	SIZE A3	CAGE CODE 00779	DRAWING NO C-2980010	RESTRICTED TO -
				SCALE 8:1	SHEET 1 OF 1	REV A1	