

NUMBER 900128



三角法 (3rd ANGLE PROJECTION)

METRIC

単位: 単位 DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DIST

AMP-J010-2C
REV. 3/93



パネル穴加工推奨寸法
RECOMMENDED PANEL HOLE LAYOUT

NOTES

- 1 PACKING UNIT : 1000 EA
- △ TWO PUSH RIVETS REQUIRED FOR MOUNTING.

注記

- 1 包装は1000個単位のこと
- △ 本製品は2個使いのこと

6.4	1.6	7	3.5	1.95	2.8~3.8	2~3 kg	13 kg MIN	900128-3
6.4	1.6	5.5	3.5	1.95	1.3~2.3	2~3 kg	13 kg MIN	900128-2
6.4	1.6	4.5	3.5	1.95	0.3~1.3	2~3 kg	13 kg MIN	900128-1
(A)	(B)	(C)	(D)	(E)	F	挿入力 (参考) INSERTION FORCE (REF)	保持力 RETENTION FORCE	型番 PARTS NUMBER

				Copyright ©1994年 AMP (Japan). LTD. 日本エー・エム・ピー株式会社				Copyright ©1994 AMP (Japan). LTD. ALL RIGHTS RESERVED.				AMP 日本エー・エム・ピー株式会社 Tokyo, Japan									
				適合電線断面積 (WIRE RANGE) mm ² (AWG -)				被覆外径 (INSULATION DIA.) mmφ				名称 (NAME) プッシュリベット ダイナミック シリーズ用 PUSH RIVET FOR DYNAMIC SERIES									
				材料 (MATERIAL) 6ナイロン: 黒色 (94V-2) 6NYLON: BLACK				仕上 (FINISH)				一般公差 (GENERAL TOLERANCE) 10以下: ±0.2 10を超え 30以下: ±0.25 30を超え 100以下: ±0.3 角 度: ±3°				LOC B J		番号 (No.) 900128			
A REVISED (FJ00-2166-95)				K. I. S. M.		B. MAKI 27/SEP/94		DR. 27/SEP/94 K. IKEDA				DE. 27/SEP/94 K. IKEDA									
O RELEASED (FJ00-0885-94)				K. I. S. M.		27/SEP/94		CHK. 27/SEP/94 S. MANABE				APP. 27/SEP/94 S. MANABE									
LTR 変更 (REVISION RECORD)				DR		CHK		DATE		CHK.		APP.				尺 度 (SCALE) 5-1		REV. A		SHEET 1 OF 1	

(CUSTOMER DRAWING) 参考 図 面