


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECN-25-354023	18NOV2025	SN	DR



- 1 WIRE RANGE IS FOR 4 AWG STANDARD WIRE CROSS SECTIONAL AREA RANGE: 33,100-52,600 CMA, STRANDED WIRE
 - 2 TERMINAL BODY MATERIAL THK IS 1.778±0.076[0.070±0.003]
 - 3 RECOMMENDED OPERATING TEMP -65°C [-85°F] TO +200°C [392°F] FOR HEAT SHRINK TUBING
 - 4 HEAT SHRINK TUBING SHELF LIFE OF 144 MONTHS FROM DATE CODE ON LABEL
- 5 TERMINAL BODY PRODUCT SPECIFICATION 108-32046. APPLICATION SPECIFICATION 114-2162

1	4-1192767-4	HIGH AND LOW TEMPERATURE CROSS LINKED FLUDROPOLYMER HEAT SHRINK TUBING 12.7[0.500] MIN ID X 37.998±1.499 [1.496±0.059], RT-555-½-0-SP
1	323173	TERMINAL BODY: COPPER PER ASTM B152 ANNEALED FINISH: NICKEL PLATE 0.00762 [0.000300] MIN EXT THK PER SAE AMS QQ-N-290
QTY	PART NO	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 29OCT09	STE TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK TOM MICHIELUTTI 29OCT09			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD TOM MICHIELUTTI 29OCT09	NAME		
0 PLC ± -		PRODUCT SPEC	HEAT RESISTANT TERMINAL KIT		
1 PLC ± -		5	WIRE SIZE: 4 AWG		
2 PLC ± -		5	-		
3 PLC ± 0.127[0.005]		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
4 PLC ± -		5	A3	00779	C-696640
ANGLES ± 1°		FINISH	RESTRICTED TO	-	
MATERIAL SEE TABLE		WEIGHT	SCALE 5:1 SHEET 1 OF 1 REV C		
SEE TABLE		CUSTOMER DRAWING			